


# 760109520 | 360G2 Cartridge 6-SC-LS-AQ-PIGTAILS B

---



360G2 Multimode OM4 Fiber Cassette 6 SC with pigtails B

## Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber cassette with pigtails
<b>Product Series</b>	G2

## General Specifications

<b>Color, front</b>	Aqua
<b>Intelligence Type</b>	Not iPatch® ready
<b>Interface, front</b>	SC/UPC
<b>Interface, rear</b>	Stranded pigtail
<b>Total Ports, quantity, front</b>	6

## Dimensions

<b>Height</b>	25.908 mm   1.02 in
<b>Width</b>	94.996 mm   3.74 in
<b>Depth</b>	123.012 mm   4.843 in

## Optical Specifications

<b>Fiber Mode</b>	Multimode
<b>Fiber Type</b>	OM4
<b>Insertion Loss, maximum</b>	0.33 dB

## Environmental Specifications

<b>Qualification Standards</b>	IEC 61753-1   TIA-568.3-D
--------------------------------	---------------------------

# 760109520 | 360G2 Cartridge 6-SC-LS-AQ-PIGTAILS B

---

**Safety Standard**

CE | CSA | UL

Packaging and Weights

**Packaging quantity**

1

Regulatory Compliance/Certifications

**Agency**

**Classification**

CHINA-ROHS

Below maximum concentration value

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant

