

# MX6-SPL6030-A-D7Z4

---



OMX® Splice Cabinet, up to 5184 fiber splices (ribbon cables), exit down, Putty white, 7 ft

## Product Classification

<b>Regional Availability</b>	Australia/New Zealand   EMEA   Latin America   North America
<b>Product Type</b>	Fiber entrance cabinet
<b>Product Brand</b>	OMX600®
<b>Product Series</b>	OMX

## General Specifications

<b>Access</b>	Front
<b>Cable Entry Location</b>	Bottom
<b>Cable Exit Location</b>	Bottom
<b>Color</b>	Putty white
<b>Mounting</b>	Raised floor
<b>Splice Trays Included, quantity</b>	0
<b>Splicing Capacity Note</b>	up to 5184 ribbon fibers
<b>Splicing Capacity, maximum</b>	5184

## Dimensions

<b>Height</b>	2,133.6 mm   84 in
<b>Width</b>	596.9 mm   23.5 in
<b>Depth</b>	299.72 mm   11.8 in

## Environmental Specifications

<b>Environmental Space</b>	Indoor
<b>Qualification Standards</b>	Seismic rating, zone 4

# MX6-SPL6030-A-D7Z4

---

## Regulatory Compliance/Certifications

**Agency****Classification**

CHINA-ROHS

Above maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.commscope.com/ProductCompliance](http://www.commscope.com/ProductCompliance)

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted

