

760031716 | iP-Power-Supply



iPatch® Power Supply 12VDC 3050 mm Power Cord

OBSOLETE

This product was discontinued on: June 8, 2018

Replaced By:

760222448

imV-Pwr-Supply

imVision® Power Supply 12VDC 3050 mm Power Cord

Product Classification

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

Portfolio

SYSTIMAX®

Product Type

Network controller accessory

Product Brand

iPatch® | imVision®

General Specifications

Color

Black

Dimensions

Height

71.12 mm | 2.8 in

Width

43.18 mm | 1.7 in

Depth

33.02 mm | 1.3 in

Electrical Specifications

Input Voltage

100–240 Vac

Output Current at Voltage, continuous

1.25 A @ 12 Vdc

Power Frequency

50–60 Hz

Material Specifications

Material Type

Polycarbonate

760031716 | iP-POWER-SUPPLY

Environmental Specifications

Operating Temperature	-5 °C to +50 °C (+23 °F to +122 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Flammability Rating	UL 94 V-0
Safety Standard	ACMA CE GB INNOVA GS PSE UL cUL

Packaging and Weights

Included	Five types AC power plugs Power supply, 12 Vdc
Packaging quantity	1
Weight, net	0.227 kg 0.5 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

