



imVision Controller X Rack Extender Kit

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Controller unit
Product Brand	iPatch® imVision®

Electrical Specifications

Input Voltage	100–240 Vac
----------------------	-------------

Environmental Specifications

Operating Temperature	0 °C to +50 °C (+32 °F to +122 °F)
Storage Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Safety Standard	CE RCM UL

Packaging and Weights

Included	13 ft panel bus jumper (two) Forty-four position bus panel (two)
Packaging quantity	1
Weight, net	1.134 kg 2.5 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

