

7640450-00



ION® Alarm Cable for Active Intelligent Point of Interface, 0.7 m inter-subrack connection

Product Classification

| | |
|----------------------|-------------|
| Product Type | Alarm cable |
| Product Brand | ION® |

General Specifications

| | |
|------------------------|---|
| Cable, quantity | 4 |
| Connector A | Crimped dc connector, female, 4 contacts |
| Connector B | Crimped connector, female, 4 contacts |
| Note | Detailed Product Specifications are available. Please contact your local ANDREW representative. |

Dimensions

| | |
|--------------------|-------------------|
| Height | 200 mm 7.874 in |
| Width | 10 mm 0.394 in |
| Depth | 250 mm 9.843 in |
| Cable Gauge | 24 AWG |

Electrical Specifications

| | |
|-----------------------------------|---------------|
| Current per Pin | 0.5 A |
| Electrical Safety Standard | EN 60950 |
| Voltage Range | +5 to +60 Vdc |

Packaging and Weights

| | |
|-----------------------|--------------------|
| Height, packed | 250 mm 9.843 in |
| Width, packed | 20 mm 0.787 in |
| Depth, packed | 300 mm 11.811 in |
| Weight, gross | 0.5 kg 1.102 lb |
| Weight, net | 0.25 kg 0.551 lb |

7640450-00

Regulatory Compliance/Certifications

Agency

ISO 9001:2015

Classification

Designed, manufactured and/or distributed under this quality management system