

AISG-T



AISG Three-way Tee

- Compatible with all Argus antennas except for the CNNPX series

OBSOLETE

This product was discontinued on: June 30, 2018

Product Classification

Product Type RET splitter

General Specifications

AISG Input Connector 8-pin DIN Male

AISG Input Connector Body Style Straight

AISG Input Connector Quantity 1

AISG Output Connector 8-pin DIN Female

AISG Output Connector Body Style Straight

AISG Output Connector Quantity 2

Color Silver

Data Conductors, quantity 2

Power Conductors, quantity 4

Total Conductors, quantity 7

Dimensions

Height 44 mm | 1.732 in

Depth 22 mm | 0.866 in

Length 48 mm | 1.89 in

Electrical Specifications

Protocol AISG 1.1 | AISG 2.0

Environmental Specifications

AISG-T

Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)
Relative Humidity	Up to 95%, non-condensing
Corrosion Test Method	IEC 60068-2-11, Test Condition Ka
Ingress Protection Test Method	IEC 60529:2001, IP67

Packaging and Weights

Weight, net	0.1 kg 0.22 lb
--------------------	------------------

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system