177SC

Fixed-tuned UG-51/U for elliptical waveguide 77

Product Classification

Product Type Elliptical waveguide connector

General Specifications

Attachment Method Tab-flare | Tool-flare

Body Style Straight, fixed-tuned

Inner Contact PlatingUnplatedInterfaceUG-51/UOuter Contact PlatingUnplatedPressurizableYes

Dimensions

 Width
 88.392 mm | 3.48 in

 Length
 92.202 mm | 3.63 in

 Transition Length
 55.118 mm | 2.17 in

 Waveguide Size
 WR112 | WG15 | R84

Electrical Specifications

Insertion Loss, typical 0.01 dB

Operating Frequency Band 7.125 – 8.5 GHz

Peak Power at Frequency, maximum 63.00 kW @ 7.80 GHz

Material Specifications

Material Type Brass

Environmental Specifications

Operating Temperature-55 °C to +85 °C (-67 °F to +185 °F)Storage Temperature-55 °C to +85 °C (-67 °F to +185 °F)

Packaging and Weights

Weight, net 1.4 kg | 3.086 lb



177SC

Regulatory Compliance/Certifications

Agency Classification

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

* Footnotes

Insertion Loss, typical 0.05√ freq (GHz) (not applicable for elliptical waveguide)

