


# 760005397 | M81-RCA-110-262-R



M81 RCA to 110 Punchdown Module Audio and Video Adapter, white housing red connector

## Product Classification

### Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

### Portfolio

CommScope®

### Product Type

Multimedia outlet

## General Specifications

### Color

White

### Color, RCA

Red

### Mounting

Snap-in

### UTP 110 Terminal Block

110 ohm

## Electrical Specifications

### Attenuation dc at Frequency, maximum

2 dB @ 5.5 MHz

### Crosstalk @ Gain at Frequency

-60 dB @ 5.5 MHz

### Impedance

75 ohm

### Insulation Resistance, minimum

50 MOhm

## Material Specifications

### Material Type

High-impact, flame retardant, thermoplastic

## Environmental Specifications

### Operating Temperature

-10 °C to +60 °C (+14 °F to +140 °F)

### Storage Temperature

-40 °C to +70 °C (-40 °F to +158 °F)

### Relative Humidity

5%–95%, non-condensing

### Flammability Rating

UL 94 V-0

## Packaging and Weights

### Packaging quantity

1

## Regulatory Compliance/Certifications

**Agency**

ISO 9001:2015

**Classification**

Designed, manufactured and/or distributed under this quality management system