

# C400-BMBM

---

Base Product



CNT-400 CNT® Jumper with interface types BNC Male and BNC Male, variable length

## Product Classification

|                       |                        |
|-----------------------|------------------------|
| <b>Product Type</b>   | Braided cable assembly |
| <b>Product Brand</b>  | CNT®                   |
| <b>Product Series</b> | CNT-400                |

## General Specifications

|   |  |
|---|--|
| <b>Attachment, Connector A</b>            | Factory attached   |
| <b>Attachment, Connector B</b>            | Factory attached   |
| <b>Body Style, Connector A</b>            | Straight   |
| <b>Body Style, Connector B</b>            | Straight   |
| <b>Cable Family</b>                       | CNT-400  |
| <b>Interface, Connector A</b>             | BNC Male   |
| <b>Interface, Connector B</b>             | BNC Male   |
| <b>Specification Sheet Revision Level</b> | A  |
| <b>Variable Length</b>                    | For custom lengths, contact your local ANDREW representative |

## Dimensions

|                     |          |
|---------------------|----------|
| <b>Nominal Size</b> | 0.400 in |
|---------------------|----------|

## VSWR/Return Loss

| Frequency Band | VSWR  | Return Loss (dB) |
|----------------|-------|------------------|
| 700–2000 MHz   | 1.222 | 20.01            |
| 2000–3000 MHz  | 1.288 | 18               |

## Jumper Assembly Sample Label

# C400-BMBM

---



## Included Products

- 400PBM-CR – BNC Male for CNT-400 braided cable
- CNT-400 – CNT-400, CNT<sup>®</sup> 50 Ohm Braided Coaxial Cable, variable, black PE jacket