

760163501 | HFTP-J5E

Uniprise HFTP-J5E Category 5e Shielded High Density Information Outlet



OBSOLETE

This product was discontinued on: February 28, 2017

Replaced By:

760163519
HFTP-J6

Uniprise HFTP-J6 Category 6 Shielded High Density Information Outlet

Product Classification

Regional Availability

North America

Portfolio

Uniprise®

Product Type

Modular jack

General Specifications

ANSI/TIA Category

5e

Application

Adapts to M Series and Keystone

Cable Type

Shielded

Color

Silver

Conductor Type

Solid | Stranded

Integrated Dust Cover Type

None

Outlet Type

High density

Termination Type

IDC

Wiring

T568A | T568B

Dimensions

Height

19.56 mm | 0.77 in

Width

17.02 mm | 0.67 in

760163501 | HFTP-J5E

Depth 33.53 mm | 1.32 in

Compatible Conductor Gauge, solid 22 AWG | 24 AWG

Compatible Conductor Gauge, stranded 22 AWG | 24 AWG

Electrical Specifications

Contact Resistance Variation, maximum 20 mOhm

Contact Resistance, maximum 100 mOhm

Current Rating at Temperature 1.5 A @ 20 °C | 1.5 A @ 68 °F

Dielectric Withstand Voltage, RMS, conductive surface 1,500 Vac @ 60 Hz

Dielectric Withstand Voltage, RMS, contact-to-contact 1,000 Vac @ 60 Hz

Insulation Resistance, minimum 500 MOhm

Material Specifications

Contact Plating Material Precious metals

Material Type Copper alloy | High-impact, flame retardant, thermoplastic | Zinc

Termination Contact Plating Nickel

Mechanical Specifications

Plug Insertion Life, minimum 750 times

Plug Insertion Life, test plug IEC 60603-7 compliant plug

Plug Retention Force, minimum 133 N | 29.9 lbf

Environmental Specifications

Operating Temperature -10 °C to +60 °C (+14 °F to +140 °F)

Storage Temperature -40 °C to +70 °C (-40 °F to +158 °F)

Relative Humidity Up to 95%, non-condensing

Flammability Rating UL 94 V-0

Safety Standard UL | cUL

Packaging and Weights

Packaging quantity 25

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

760163501 | HFTP-J5E

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant



Included Products

760154187 - High Density M-Series Adapter, white
HGS-A-MS-WHITE