NPC6ASZDB

Base Product



NETCONNECT® Cat 6A S/FTP RJ45 Patch Cord, LSZH

- High-performance patch cords exceeding industry standards supporting NETCONNECT channel specifications
- Standardized transparent, slim-line boots provides consistent patch cord appearance and supports highest density applications
- Colored clips are available to fit the transparent boot, eliminating the need of multiple colors for matching every jacket color
- Colored pull latch tabs are available for easier plug release handling from the modular jack

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America		
Portfolio	NETCONNECT®		
Product Type	Twisted pair patch cord		
Product Series	NPC		
Ordering Note	Cords < 1 m are valid elements for use in a channel or as an equipment interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords Cords > 1 m are authorized for use in channels and are an effective standalone method used to connect active devices		
General Specifications			
ANSI/TIA Category	6A		
Cable Type	S/FTP (shielded)		

Cable Type	S/FTP (shielded)
Conductor Type	Stranded
Interface, Connector A	RJ45 plug
Interface Feature, connector A	Standard
Interface, Connector B	RJ45 plug
Interface Feature, connector B	Standard
Jacket Color	Black Blue Gray Green Orange Red Violet White Yellow
Pairs, quantity	4
Transmission Standards	ANSI/TIA-568.2-D ISO/IEC 11801 Class EA
Wiring	T568B

Dimensions

Page 1 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 9, 2025



NPC6ASZDB

Cable Assembly Length Range (m)	1 – 30
Cable Assembly Length Range (ft)	1 - 100
Cable Assembly Length Range (cm)	15 – 999
Cable Assembly Length Range (in)	6 - 999
Diameter Over Jacket	5.84 mm 0.23 in
Compatible Conductor Gauge, stranded	26 AWG

Electrical Specifications

Remote Powering

Fully supports the safe delivery of power over LAN cabling described by IEEE 802.3bt (Type 4) and complies with the unmating under electrical load requirements prescribed by IEC 60512-99-002

Supports IEEE 802.3bt Type 4 (90 W) applications greater than 3000 plug to jack

PoE Durability

Safety Voltage Rating

300 V

mating cycles

Ordering Tree

N	PC				12 11 0 5 0 M	1
Jack	et Color	R.	UON	١		Length
10	BK	Black		F	Foot	12 XXX
10	BL	Blue	- 11	М	Meter	
	GN	Green		Ν	Inch	
	GY	Gray		С	Centimeter	
	OR	Orange				
	РК	Pink	Note	S		
	RD	Red	 Cords > 1m are authorized for use in channels and are an effective standalone method used to connect active devices 			
	VT	Violet				
	WT	White	• Corc	 Cords < 1m are also valid elements for use in a channel or as an equipment 		
	YL	Yellow	interconnect but due to their limited length are not guaranteed to meet component compliance requirements that were developed to assess the quality of longer cords			
			com	pliance r	equirements that wer	e developed to assess the quality of longer cords

Mechanical Specifications

Plug Retention Force, minimum	133 N 29.9 lbf
Plug to Jack Mating Cycles	Complies to IEC 60603-7 series

Environmental Specifications

Operating Temperature

Relative Humidity

-20 °C to +60 °C (-4 °F to +140 °F)

Up to 93%, non-condensing

Page 2 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 9, 2025



NPC6ASZDB

Environmental Space

Safety Standard

Packaging and Weights

Packaging quantity

1

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
RCM	Compliant to electrical safety & telecommunications requirements
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant
<u>@</u> 🔕	

Included Products

2843032-3 MP-Boot-S/SL-AB	-	Modular Plug Shielded Slim-Line Boot for Category 6A/6 and Category 5e EMT Plugs, 4.7 to 6.0 mm, transparent
6-2111981-3 MP-6AS-B-1	-	Modular Plug Kit, category 6A, shielded, 8-position, 5.1 – 6.0 mm max cable jack OD, 100/bag

Low Smoke Zero Halogen (LSZH)

Anatel | UL 1863

Page 3 of 3

©2025 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 9, 2025

