

# 48939A-17

---



Boot Assembly, 5 in, for four 1/2 in corrugated coaxial cable

## Product Classification

<b>Product Type</b>	Boot assembly
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	ANDREW® non-standard product

## General Specifications

<b>Cable Type</b>	Corrugated
<b>Cables per Cushion</b>	4
<b>Color</b>	Black

## Dimensions

<b>Height</b>	127 mm   5 in
<b>Length</b>	76.2 mm   3 in
<b>Nominal Size</b>	1/2 in

## Material Specifications

<b>Material Type</b>	EPDM rubber
----------------------	-------------

## Environmental Specifications

<b>UV Resistance Test Method</b>	MIL-STD-810E, Procedure 11, Method 505
<b>UV Resistance, minimum with no degradation</b>	≥1000 hours
<b>Weather Resistance Test Method</b>	04AS00-03.9.0   IEC 60529:2001, IP66

## Packaging and Weights

<b>Height, packed</b>	190.5 mm   7.5 in
<b>Width, packed</b>	170.18 mm   6.7 in
<b>Length, packed</b>	78.74 mm   3.1 in
<b>Included</b>	Boot   Cushion   Two clamps

# 48939A-17

---

**Packaging quantity** 1  
**Weight, gross** 0.9 kg | 1.984 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant