

19256B-C



Lace-up Hoisting Grip with tie wrap for HELIAX® 1.00-1.24 in (25.4-31.5 mm) cables, elliptical waveguide 77

Product Classification

Product Type	Hoisting grip
Product Brand	HELIAX®
Ordering Note	ANDREW® non-standard product

General Specifications

Attachment Spacing Intervals	60.96 m 200 ft
Hoisting Grip Type	Lace-up hoisting grip
Support Clamp	Not included
Tool Type	Hoisting grip

Dimensions

Grip Length, minimum	431.8 mm 17 in
Leader Length, minimum	330.2 mm 13 in
Compatible Diameter, maximum	31.5 mm 1.24 in
Compatible Diameter, minimum	25.4 mm 1 in
Nominal Size	7/8 in

Electrical Specifications

Return Loss Effect, maximum	0.1 dB
DTF Effect, maximum	0.1 dB

Material Specifications

Material Type	Stainless steel
----------------------	-----------------

Mechanical Specifications

Pull Load Capacity	226.796 kg 500 lb
---------------------------	---------------------

19256B-C

Packaging and Weights

Height, packed	38.1 mm 1.5 in
Width, packed	218.44 mm 8.6 in
Length, packed	220.98 mm 8.7 in
Packaging quantity	1
Weight, gross	0.22 kg 0.485 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.andrew.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant