655694-000 | T-DUX-150



TDUX - Inflatable Duct Seal, size 150

- Flexible and reliable wraparound inflatable sealing system for cables
- Fast and easy to install or remove, even when water is flowing out of the duct
- Independent of duct or cable ovality
- Water and airtight up to 50 kPa (7 psi)
- Environmentaly friendly, non-toxic and resistant to chemicals

Product Classification

Regional Availability Latin America | North America

Product Type Cable duct seal

Product Series TDUX

Ordering Note When sealing more than two cables in a duct, seperate orderable TDUX-CL clips are to be

used

Dimensions

Width 120 mm | 4.724 in

Length 667 mm | 26.26 in

Cable Diameter, maximum 114.3 mm | 4.5 in

Cable Diameter, minimum 101.6 mm | 4 in


Conduit Inner Diameter, maximum 152.4 mm | 6 in

Conduit Inner Diameter, minimum 139.7 mm | 5.5 in

Dimension Drawing



655694-000 | T-DUX-150



Environmental Specifications

Installation temperature $-5 \,^{\circ}\text{C}$ to +40 $^{\circ}\text{C}$ (+23 $^{\circ}\text{F}$ to +104 $^{\circ}\text{F}$)

Packaging and Weights

Included Inflatable bladder with sealing mechanism

Packaging quantity 10

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

