


CL-0920-U



Universal Cable Ladder Kit, 30 in x 20 ft, 9-hole rung

Product Classification

Product Type Ladder kit

General Specifications

Cable Runs, quantity 9

Mounting Round and angle legs

Dimensions


Height 76.2 mm | 3 in

Width 762 mm | 30 in

Length 6096 mm | 240 in

CL-0920-U

Outline Drawing



Material Specifications

Material Type Hot dip galvanized steel

Packaging and Weights

Included Attachment kits | Ladder | Splice plates

Packaging quantity 1

Weight, net 52.9 kg | 116.624 lb

Regulatory Compliance/Certifications

Agency **Classification**

CL-0920-U

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

Included Products

- HK-CL-U – Universal Cable Ladder Hardware Kit for 1 in to 4-1/2 in round or angle members

HK-CL-U



Universal Cable Ladder Hardware Kit for 1 in to 4-1/2 in round or angle members

Product Classification

| | |
|----------------------|-----------------------------------|
| Product Type | Ladder kit |
| Ordering Note | ANDREW® standard product (Global) |

General Specifications

| | |
|-----------------------------|----------------------|
| Cable Runs, quantity | 0 |
| Mounting | Round and angle legs |

Dimensions

| | |
|-----------------------------------|-------------------|
| Height | 203.2 mm 8 in |
| Width | 127 mm 5 in |
| Length | 203.2 mm 8 in |
| Mounting Diameter, maximum | 114.3 mm 4.5 in |
| Mounting Diameter, minimum | 25.4 mm 1 in |

Material Specifications

| | |
|----------------------|--------------------------|
| Material Type | Hot dip galvanized steel |
|----------------------|--------------------------|

Packaging and Weights

| | |
|---------------------------|-------------------|
| Included | J-bolts Plates |
| Packaging quantity | 1 |
| Weight, net | 1.7 kg 3.748 lb |

Regulatory Compliance/Certifications

| Agency | Classification |
|---------------|--|
| CHINA-ROHS | Above maximum concentration value |
| ISO 9001:2015 | Designed, manufactured and/or distributed under this quality management system |
| ROHS | Compliant/Exempted |

HK-CL-U

UK-ROHS

Compliant/Exempted

