



## OCAB Outdoor fiber distribution cabinet

- OCAB cabinets offers dust-proof, environmental and mechanical protection for the fiber management functions of splicing, patching and passive component integration
- Anti-vandalism features such as IK10 stainless steel material rating, reinforced door hinges preventing door removal and anti-graffiti paint finish (optional)
- Easy installable and wingnut-secured in-let plates can be custom-configured, selecting the amount of incoming, outgoing ports and PG gland sizes
- Removable top roof for possible future upgrades
- Possibility for infield repair, removable cabinet body
- Various accessories such as plinths and in-ground roots

Drop cabinet for up to 144f customer connections

- 96 up to 144 Point-to-multipoint positions, SC & LC footprint
- 8 branch-off blown fibre Ø5,7& 8mm microtube positions
- 4 branch-off blown fibre Ø 12mm microtube positions
- 144 direct drops blown fibre Ø5,7 & 8mm microtube positions
- Up to 12 OCM1 LGX Style Fiber Optic Splitter Module positions
- Transient-free, modular, flexible fibre management
- FIST single-circuit and single-element splice trays
- Up to 768 splices (including SC trays 256 splices)
- Storage area for looped cable
- Compatible with all fibre types: G.652D and G.657 series
- Fast and simple installation

## Product Classification

<b>Regional Availability</b>	EMEA
<b>Product Type</b>	Fiber cross-connect hub
<b>Product Series</b>	OCAB

## General Specifications

<b>Access</b>	Front   Single door
<b>Color</b>	Light Gray (RAL 7035)
<b>Mounting</b>	In-ground root   Pre-fabricated base

## Dimensions

<b>Height</b>	981.4 mm   38.638 in
<b>Width</b>	780 mm   30.709 in
<b>Depth</b>	314.5 mm   12.382 in
<b>Enclosure Size</b>	Medium

## Material Specifications

<b>Finish</b>	Powder coated polyester
<b>Material Type</b>	Stainless steel grade 1.4003, 1.5 mm gauge, welded construction

## Environmental Specifications

<b>Environmental Space</b>	Above ground
<b>Qualification Standards</b>	IEC 60529, IP54   IK10

## Packaging and Weights

<b>Packaging quantity</b>	5
<b>Packaging Type</b>	Pallet

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ROHS	Compliant

