

# SSH-M

---



SnapStak® Plus Adjustable Hanger for 14+mm to 25mm Cable - No Grommets Required. For patents, see [www.cs-pat.com](http://www.cs-pat.com).

## Product Classification

<b>Product Type</b>	Hanger kit
<b>Product Brand</b>	SnapStak® Plus
<b>Ordering Note</b>	ANDREW® non-standard product

## General Specifications

<b>Accessories</b>	Hangers
<b>Cables per Hanger</b>	1
<b>Color</b>	Silver
<b>Hanger Type</b>	Snap-in hanger
<b>Mounting</b>	3/4 in drilled cable ladder
<b>Patent Number</b>	US 9,866,004

## Dimensions

<b>Maximum Stack Height</b>	2
<b>Maximum Stack Height, Coaxial</b>	2
<b>Height</b>	67.1 mm   2.642 in
<b>Width</b>	38.1 mm   1.5 in
<b>Length</b>	48.5 mm   1.909 in
<b>Compatible Cable Diameter Range</b>	14–25 mm
<b>Compatible Diameter, maximum</b>	25 mm   0.984 in
<b>Compatible Diameter, minimum</b>	14 mm   0.551 in

## Electrical Specifications

<b>Return Loss Effect, maximum</b>	0.1 dB
<b>DTF Effect, maximum</b>	0.1 dB

## Material Specifications

# SSH-M

---

**Material Type** Stainless steel

## Mechanical Specifications

**Vibration Survival** ≥4 hours at resonant frequency

## Environmental Specifications

**Operating Temperature** -40 °C to +85 °C (-40 °F to +185 °F)

**Corrosion Resistance, minimum with no degradation** ≥1000 hours in salt spray chamber

**Environmental Strength Capability** Double cable weight

**Flammability Test Method** UL 2043

## Packaging and Weights

**Height, packed** 33 cm | 12.992 in

**Width, packed** 6.4 cm | 2.52 in

**Length, packed** 26 cm | 10.236 in

**Packaging quantity** 10

**Weight, gross** 0.53 kg | 1.168 lb

## Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.andrew.com/ProductCompliance">www.andrew.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## \* Footnotes

**Maximum Stack Height** Fiber, Hybrid, Power