


UGBA-DIN-34



Universal Ground Bar Assembly, three four-position ground bars, for 7-16 DIN or bolt-grounded surge arrestors

OBSOLETE

Product Classification

Product Type	Grounding bar
Ordering Note	CommScope® non-standard product

Dimensions

Height	50.8 mm 2 in
Length	723.9 mm 28.5 in
Material Thickness	3.175 mm 0.125 in
Hole Size	1.3 in
Hole Distance, center to center	137.16 mm 5.4 in

Material Specifications

Material Type	Copper
----------------------	--------

Packaging and Weights

Height, packed	1016 mm 40 in
Width, packed	63.5 mm 2.5 in
Length, packed	63.5 mm 2.5 in
Included	Bulkhead mounting bar Grounding bar Insulators Mounting brackets Threaded rod Universal hardware
Packaging quantity	1
Weight, gross	8.6 kg 18.96 lb

Regulatory Compliance/Certifications

Agency	Classification
---------------	-----------------------

UGBA-DIN-34

CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant
UK-ROHS	Compliant

