



Torch Handle Tool Kit with piezo-burner heads, safety valve and 4m high pressure hose

- Ideally suited for handling all heat shrink based copper closures
- Progressive regulation, stable flow rate of propane and/or butane
- Flexible connection of gas tube to the handle allows easy handling
- Air regulator to obtain the right flame color ratio (blue/yellow)

OBSOLETE

This product was discontinued on: June 30, 2022

Product Classification

Regional Availability EMEA

Product Type Tool

General Specifications

Application For use with copper/fiber closures with heat shrink cable ports

Dimensions

Height 74 mm | 2.913 in

Width 210 mm | 8.268 in

Length 470 mm | 18.504 in

Material Specifications

Material Type Aluminum

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Carton

Weight, net 4.8 kg | 10.582 lb

Included Products

149567-000 – Safety Regulator for Torch Tool

187225N001 | FH-1630-PIE-MC10

- FH-1630-PIE-LGS
- 201385-000 – Burner Head for Torch Tool, 38 mm nozzle
- FH-1630-PIE-BN38
- 299247-000 – High Pressure Hose for Torch Tool, 4 meters
- FH-1630-PIE-SW4
- 354957-000 – Burner Head for Torch Tool, 50 mm nozzle
- FH-1630-PIE-BN50
- 660983-000 – Handgrip Burner handle, piezo-electric for Torch Tool
- FH-1630-PIE
- 983099-000 – Burner Head for Torch Tool, 28 mm nozzle
- FH-1630-PIE-BN28