

# 286311-000 | FH-1630-S-MC10



Torch Handle Tool Kit with burner heads, safety valve and 4m high pressure hose

- Ideally suited for handling all heat shrink based copper closures
- Progressive regulation, stable flow rate of propane and/or butane
- Flexible connection of gas tube to the handle allows easy handling
- Air regulator to obtain the right flame color ratio (blue/yellow)

## OBSOLETE

This product was discontinued on: June 30, 2022

## Product Classification

**Regional Availability** EMEA

**Product Type** Tool

## General Specifications

**Application** For use with copper/fiber closures with heat shrink cable ports

## Dimensions

**Height** 74 mm | 2.913 in

**Width** 210 mm | 8.268 in

**Length** 470 mm | 18.504 in

## Material Specifications

**Material Type** Aluminum

## Packaging and Weights

**Packaging quantity** 1

**Packaging Type** Bag | Carton

**Weight, net** 4.8 kg | 10.582 lb

## Included Products

295849-000 – Burner Head for Torch Tool, 28 mm nozzle  
FH-1630-S-BN28

# 286311-000 | FH-1630-S-MC10

---

- 299247-000 – High Pressure Hose for Torch Tool, 4 meters  
FH-1630-PIE-SW4
- 414431-000 – Pressure Regulator for Torch Tool  
FH-1630-PIE-R1
- 651823-000 – Automatic shut-off Valve for Torch Tool  
FH-1630-PIE-CV
- 839029-000 – Handgrip Burner handle for Torch Tool  
FH-1630-S-HSZ
- 918209-000 – Burner Head for Torch Tool, 28 mm nozzle  
FH-1630-S-BN38