

RK-36-3M



Monopole Load Distribution Reinforcement Kit, 3 Sector, 15" to 50" OD, 36" Kicker

Product Classification

Product Type Reinforcement kit

General Specifications

Mounting Monopole, 381–1270 mm (15–50 in) OD

Sectors, quantity 3

Dimensions

Height 254 mm | 10 in

Length 914.4 mm | 36 in

Mounting Diameter, maximum 1270 mm | 50 in

Mounting Diameter, minimum 381 mm | 15 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative

Packaging and Weights

Included Attachment hardware | Ring mount

Packaging quantity 1

Weight, net 142.882 kg | 315 lb

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Above maximum concentration value
ROHS	Compliant/Exempted

RK-36-3M

UK-ROHS

Compliant/Exempted



* Footnotes

Wind Rating

BWS—Base Wind Speed; FBC—Florida Building Code