RK-36-4S



Monopole Load Distribution Reinforcement Kit, 4 Sector, 10" to 30" OD, 36" Kicker

Product Classification

Product Type Reinforcement kit

General Specifications

Mounting Monopole, 254–762 mm (10–30 in) OD

Sectors, quantity 4

Dimensions

 Height
 254 mm | 10 in

 Length
 914.4 mm | 36 in

 Mounting Diameter, maximum
 762 mm | 30 in

 Mounting Diameter, minimum
 254 mm | 10 in

Material Specifications

Material Type Hot dip galvanized steel

Mechanical Specifications

Wind Rating For Specifications, please contact your local ANDREW representative

Packaging and Weights

Included Attachment hardware | Ring mount

Packaging quantity 1

Weight, net 131.995 kg | 291 lb

Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Above maximum concentration value

REACH-SVHC Compliant as per SVHC revision on www.andrew.com/ProductCompliance



RK-36-4S

ROHS

Compliant/Exempted

UK-ROHS

Compliant/Exempted



* Footnotes

Wind Rating

BWS-Base Wind Speed; FBC-Florida Building Code

