

# RR-FA2



## Fast Access RRU Mount Kit for Back-to-Back (B2B) Mounting of (2) RRUs to Round, Straight or Tapered members

The RR-FA2 is a fast access remote radio mount bracket.

It is designed to provide a secure and efficient mounting solution for remote radio head units.

The RR-FA2 mount bracket features a revolutionary key hole located on the clamp that allows the radio and mount bracket assembly to slide perfectly into the clamp keyhole and relieves the operator from equipment weight load.

The new EZ Install design allows the brackets to be mounted to the radio prior to installation on the tower, and painlessly installed onto the tower reducing the chance of damage.

Supports all typical RRH units from Ericsson, Nokia, Samsung and Fujitsu. Ericsson radio application may also require the additional 860677769-001 interface adapter in some regions.

## Product Classification

<b>Product Type</b>	Remote radio head unit mount
<b>Ordering Note</b>	ANDREW® standard product with terms
<b>Warranty</b>	One year

## General Specifications

<b>Mounting</b>	Round and angle legs
<b>Radio Compatibility, Ericsson</b>	(2) RRUS11/12/32, 2212, 4415, 4426, 4478   4415   4435   4449   4460   4467   4480   4890   88
<b>Radio Compatibility, Nokia</b>	AHBCA   AHBCC   AHCA   AHEJ   AHFB   AHFIA   AHFIB   AHFIC   AHGB   AHHA   AHIA
<b>Radio Compatibility Samsung</b>	RF4402D-D1A   RF4437D   RF4439D   RF4440D   RF4442D   RFV01U-D1A   RFV01U-D2A   RT220T
<b>Tower Taper</b>	Non-tapered   Tapered

## Dimensions

<b>Height</b>	416.56 mm   16.4 in
<b>Length</b>	457.2 mm   18 in
<b>Mounting Diameter 2, maximum</b>	152.4 mm   6 in
<b>Mounting Diameter 2, minimum</b>	38.1 mm   1.5 in
<b>Mounting Diameter, maximum</b>	142.24 mm   5.6 in
<b>Mounting Diameter, minimum</b>	60.96 mm   2.4 in

# RR-FA2

---

## Material Specifications

**Material Type** Hot dip galvanized steel

## Packaging and Weights

**Included** Clamps | Hardware

**Packaging quantity** 2

**Weight, net** 16.329 kg | 36 lb

## Regulatory Compliance/Certifications

### Agency

### Classification

CHINA-ROHS

Below maximum concentration value

REACH-SVHC

Compliant as per SVHC revision on [www.andrew.com/ProductCompliance](http://www.andrew.com/ProductCompliance)

ROHS

Compliant

UK-ROHS

Compliant



## \* Footnotes

### Warranty

For more information, please consult our Product Warranty guidelines