

# 760053207 | KIT-CLEANING



## Cleaning Consumables Kit, Fiber Optic

### Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber cleaning and inspection kit

### General Specifications

<b>Compatible Interface</b>	LC   MPO   SC   ST
-----------------------------	--------------------

### Packaging and Weights

<b>Included</b>	(2x) Forty cleaning swabs, 1.25 mm   (2x) Forty cleaning swabs, 2.5 mm   Fiber cleaning solution, 3 oz   Instruction sheet   LC I.B.C.   MTP/MPO I.B.C   Reel cleaner refill (six per pack)   SC I.B.C.
-----------------	---

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant



### Included Products

1918806-1	- Reel cleaner refill (six per pack)
1918809-1	- Fiber Optic MTP/MPO IBC (In Bulkhead Cleaner)
2064499-1	- Fiber Optic SC IBC (In Bulkhead Cleaner)
2064500-1	- Fiber Optic LC IBC (In Bulkhead Cleaner)

## Reel cleaner refill (six per pack)



### Product Classification

<b>Regional Availability</b>	Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber cleaning kit

### General Specifications

<b>Color</b>	Blue
<b>Compatible Connector Type</b>	FC   LC   MPO (female)   MT-RJ (female)   SC   ST

### Environmental Specifications

<b>Environmental Space</b>	Indoor
----------------------------	--------

### Packaging and Weights

<b>Packaging quantity</b>	6
---------------------------	---

### Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant



## Fiber Optic MTP/MPO IBC (In Bulkhead Cleaner)



- Cleans male or female MTP/MPO connectors
- Handles more than 400 cleanings per cleaner

### Product Classification

<b>Regional Availability</b>	Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber cleaning kit

### General Specifications

<b>Color</b>	Blue
--------------	------

### Dimensions

<b>Height</b>	56.5 mm   2.224 in
<b>Width</b>	22 mm   0.866 in
<b>Length</b>	184.2 mm   7.252 in

### Environmental Specifications

<b>Environmental Space</b>	Indoor
----------------------------	--------

### Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant



## Fiber Optic SC IBC (In Bulkhead Cleaner)



- Simple pushing motion to engage tool
- Audible CLICK to alert the operator when tools is fully engaged
- Dry cleaning strand eliminates the need for solvents to be effective
- Over 525+ engagements per unit

## Product Classification

<b>Regional Availability</b>	Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber cleaning kit

## General Specifications

<b>Color</b>	Blue
<b>Interface</b>	SC

## Environmental Specifications

<b>Environmental Space</b>	Indoor
----------------------------	--------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Above maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant/Exempted





Fiber Optic LC IBC (In Bulkhead Cleaner)

## Product Classification

<b>Regional Availability</b>	Australia/New Zealand   Latin America   North America
<b>Portfolio</b>	NETCONNECT®
<b>Product Type</b>	Fiber cleaning kit

## General Specifications

<b>Color</b>	Blue
<b>Interface</b>	LC

## Dimensions

<b>Height</b>	17.5 mm   0.689 in
<b>Width</b>	17.5 mm   0.689 in
<b>Length</b>	181 mm   7.126 in

## Environmental Specifications

<b>Environmental Space</b>	Indoor
----------------------------	--------

## Packaging and Weights

<b>Packaging quantity</b>	1
---------------------------	---

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant

