MTC401548H



H-Frame, 4ft long with 2 Posts (no ice canopy)

Product Classification

Product Type	Ice canopies and shields

Dimensions

Height	4,076.7 mm | 160.5 in
Width	177.8 mm | 7 in
Length	1,219.2 mm | 48 in

Material Specifications

Material Type	Hot dip galvanized steel

Packaging and Weights

Included	Hardware | Legs | Unistrut
Packaging quantity	1
Weight, net	117 kg | 257.941 lb

Regulatory Compliance/Certifications

Agency	Classification
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Included Products

MF-130 – Direct Burial Pipe Column, 13 ft 4 in

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: June 5, 2024

MF-130



Direct Burial Pipe Column, 13 ft 4 in

Product Classification

Product Type	Pipe column

General Specifications

Application	Direct burial
Mounting	Waveguide bridge support bracket
Pipe, quantity	1

Dimensions

Height	4064 mm | 160 in
Width	88.9 mm | 3.5 in
Length	88.9 mm | 3.5 in
Pipe Length	4,053.84 mm | 159.6 in
Pipe Outer Diameter	88.9 mm | 3.5 in

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 18, 2024

MF-130

Outline Drawing



Material Specifications

Material Type	Hot dip galvanized steel

Packaging and Weights

Included	Anchors | Pipe
Packaging quantity	1
Weight, net	45.8 kg | 100.972 lb

Regulatory Compliance/Certifications

Agency	Classification

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 18, 2024

MF-130

CHINA-ROHS	Above maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
ROHS	Compliant/Exempted
UK-ROHS	Compliant/Exempted

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 18, 2024