TES-SS-PLK7 | MONOPOLE COLLAR MOUNT ASSEMBLY



Collar / Ring Mount for 12″ to 45″ OD Monopoles with 6″ x 6″ x 5/8″ bolt pattern

Product Classification

Product Type	Universal ring mount

General Specifications

Pipe, quantity	0
Sectors, quantity	3

Dimensions

Mounting Diameter, maximum	45 in | 1,143 mm
Mounting Diameter, minimum	12 in | 304.8 mm

Material Specifications

Material Type	Hot dip galvanized steel

Packaging and Weights

Included	Ring mount | Threaded rod
Packaging quantity	1

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: May 14, 2024