

Adapter Pack, 1000-type, with 12 OptiSPEED® MM duplex LC adapters, beige



## Product Classification

<b>Portfolio</b>	CommScope®
<b>Brand</b>	OptiSPEED®
<b>Product Series</b>	1000-style
<b>Product Type</b>	Fiber adapter pack
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Construction Materials

<b>Fiber Mode</b>	Multimode
-------------------	-----------

## General Specifications

<b>Interface</b>	LC
<b>Body Style</b>	Duplex
<b>Interface Feature</b>	Standard
<b>Adapter Color</b>	Beige
<b>Shuttered</b>	Yes
<b>Adapter Cutout, quantity</b>	24
<b>Adapters, quantity</b>	12
<b>Application</b>	Used in conjunction with G2 1U, 2U and 4U adapter panel shelves, surface mount and raised floor enclosures

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system



## Included Products

760056010 | MFA-LC02-BG/LP-SHUTTERED — OptiSPEED® LC Duplex Low Profile Shuttered Adapter, Beige, Single Pack

OptiSPEED® LC Duplex Low Profile Shuttered Adapter, Beige, Single Pack



## Product Classification

<b>Portfolio</b>	CommScope®
<b>Brand</b>	OptiSPEED®
<b>Product Series</b>	MFA
<b>Product Type</b>	Fiber adapter
<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Construction Materials

<b>Alignment Sleeve Material</b>	Phosphorous bronze
<b>Fiber Mode</b>	Multimode

## General Specifications

<b>Interface</b>	LC
<b>Body Style</b>	Duplex
<b>Interface Feature</b>	Reduced footprint
<b>Color</b>	Beige
<b>Package Quantity</b>	1
<b>Shuttered</b>	Yes
<b>Total Ports, quantity</b>	2
<b>Transmission Standards</b>	TIA/EIA-568-B.3   TIA/EIA-604 FOCIS-3

## Mechanical Specifications

<b>Mount Type</b>	No flange
-------------------	-----------

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

