



360G2 Cassette 12 LC Angled Singlemode Green with Pigtails iPatch Ready

Product Classification

| | |
|------------------------------|---|
| Portfolio | CommScope® |
| Product Type | Fiber cassette with pigtails |
| Regional Availability | Asia Australia/New Zealand EMEA Latin America North America |

Construction Materials

| | |
|-------------------------------|---|
| Fiber Type | G.652.D and G.657.A1 , TeraSPEED® OS2 |
| Total Fibers, quantity | 12 |

Dimensions

| | |
|-----------------------|---------------------|
| Depth | 119.38 mm 4.70 in |
| Height | 30.48 mm 1.20 in |
| Pigtail Length | 1.5 m 4.9 ft |
| Width | 91.44 mm 3.60 in |

Environmental Specifications

| | |
|------------------------|----|
| Safety Standard | UL |
|------------------------|----|

General Specifications

| | |
|-------------------------------------|---------------|
| Interface, front | LC |
| Adapter Color | Green |
| Intelligence Type | iPatch® ready |
| Interface Feature, front | Standard |
| Package Quantity | 1 |
| Total Ports, quantity, front | 12 |

Optical Performance

| | |
|--------------------------------|---------|
| Insertion Loss, typical | 0.40 dB |
| Return Loss, minimum | 65.0 dB |

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2015

Classification

Compliant
Designed, manufactured and/or distributed under this quality management system



Included Products

- 860387844 (Product Component—not orderable) — TeraSPEED® LC APC 0.9 mm Pigtail, blue, 1.5 m
- 760095596 | X-TB-8W-BL-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
 - 760211201 | X-TB-8G-BL-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
- 860387851 (Product Component—not orderable) — TeraSPEED® LC APC 0.9 mm Pigtail, orange, 1.5 m
- 760095604 | X-TB-8W-OR-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
 - 760211219 | X-TB-8G-OR-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
- 860387869 (Product Component—not orderable) — TeraSPEED® LC APC 0.9 mm Pigtail, green, 1.5 m
- 760095612 | X-TB-8W-GR-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 860387877 (Product Component—not orderable) — TeraSPEED® LC APC 0.9 mm Pigtail, brown, 1.5 m
- 760095620 | X-TB-8W-BR-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 860387885 (Product Component—not orderable) — TeraSPEED® LC APC 0.9 mm Pigtail, slate, 1.5 m
- 760095638 | X-TB-8W-SL-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 860387893 (Product Component—not orderable) — TeraSPEED® LC APC 0.9 mm Pigtail, white, 1.5 m
- 760095646 | X-TB-8W-WH-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 860387901 (Product Component—not orderable) — TeraSPEED® LC APC 0.9 mm Pigtail, red, 1.5 m
- 760095653 | X-TB-8W-RD-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 860387919 (Product Component—not orderable) — TeraSPEED® LC APC 0.9 mm Pigtail, black, 1.5 m
- 760095661 | X-TB-8W-BK-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 860387927 (Product Component—not orderable) — TeraSPEED® LC APC 0.9 mm Pigtail, yellow, 1.5 m
- 760038570 | X-TB-8W-YL-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
 - 760200568 | X-TB-8G-YL-F/G (Product Component—not orderable) — 900µm Tight Buffered Fiber
- 860387935 (Product Component—not orderable) — TeraSPEED® LC APC 0.9 mm Pigtail, violet, 1.5 m
- 760095679 | X-TB-8W-VI-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 860387943 (Product Component—not orderable) — TeraSPEED® LC APC 0.9 mm Pigtail, rose, 1.5 m
- 760095687 | X-TB-8W-RS-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber
- 860387950 (Product Component—not orderable) — TeraSPEED® LC APC 0.9 mm Pigtail, aqua, 1.5 m
- 760095695 | X-TB-8W-AQ-F/G (Product Component—not orderable) — TeraSPEED® 900µm Tight Buffered Fiber

760109504 | 360G2 Cassette 12-LCA-SM-GR-Pigtails

760066639 | AFA-LC12-GR-10-BULK-PACK-SHUTTERED — TeraSPEED® LC-APC Multiport Shuttered Adapter, Green, 10 Bulk Pack