Base Product



NOVUX[™] CSC Compact Splice Closures with gel sealing technology

Designed for FTTX drop applications, NOVUX[™] CSC100 and CSC40 compact closures are easily configurable and are available in high volumes to meet demand. From the beginning, NOVUX[™] CSC100 and CSC40 compact closures were designed for ease of installation and access. And because we began with that goal in mind, your technicians will love the way this totally new component simplifies their fieldwork. Featuring built-in mounting clips and straps, they're easily and quickly mounted on nearly any surface. And to ease installation and maintenance, CommScope's mounting bracket can be used in all applications.

NOVUX[™] CSC100 and CSC40 compact closures come with a QR code that allows installers to access CommScope's cTrak® app. With one click, cTrak provides a wealth of product information, specifications, installation instructions, videos, schematics, and test results. NOVUX[™] CSC100 and CSC40 compact closures offer an optional customer configurable ID plate to ease network record-keeping.

The CSC100 closure is offered in two types:

- CSC3: Color is black (RAL 9005)
- CSC4: Color is gray (RAL 7035)

The CSC40 closure is offered in two types:

- CSC1: Color is black (RAL 9005)
- CSC2: Color is gray (RAL 7035)

Key features of the NOVUX[™] closures:

- NOVUX[™] is the industry's most flexible FTTX platform. It takes modularity to new levels with technologies that span the end-tofiber network from the trunk to the drop. That makes it the go-to FTTX platform for virtually every application today and in the future.
- NOVUX[™] was designed from the ground up to help service providers gain access to the supplies they need –when and where they need them. And with the power of CommScope's global supply chain, service providers can trust that they'll be able to tackle even the largest FTTX deployments.
- With NOVUX[™], ordering, configuration, and training are all easier on the service provider's staff. With common components and installation procedures, it helps overcome craft labor shortages and reduce field errors, too.

Product Classification

Regional Availability	Asia EMEA Latin America North America
Product Type	Single-ended, rectangular fiber closure
Product Brand	NOVUX™
Product Series	CSC 100 CSC 40

Page 1 of 2


©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 5, 2024



General Specifications

Cable Ports Quantity, total	3 round ports + 6 multi-out ports (12 cables)
Cable Sealing Type	Compressed gel
Closure Sealing Type	Hinged with latch
Closure Style	Single-ended
Mounting	Pole Wall

Ordering Tree



Environmental Specifications

Environmental Space

Outdoor

UV Resistance

UV stabilized

Regulatory Compliance/Certifications

Classification

ISO 9001:2015

Agency

Designed, manufactured and/or distributed under this quality management system

Page 2 of 2

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 5, 2024

