


760032227 | MODG2-6SC-LS-PT-A



G2 Modular Cassette with 6 SC LazrSPEED® 550 Pigtails, Type A

OBSOLETE

Replaced By:

760109512

360G2 Cartridge 6-SC-LS-AQ-PIGTAILS A

360G2 Multimode OM4 Fiber Cassette 6 SC with pigtails A

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	SYSTIMAX®
Product Type	Fiber cassette with pigtails
Product Brand	LazrSPEED®

General Specifications

Adapter Color	Aqua
Interface, front	SC/UPC
Interface, rear	Stranded pigtail
Total Fibers, quantity	6
Total Ports, quantity, front	6

Dimensions

Height	30.48 mm 1.2 in
Width	91.44 mm 3.6 in
Depth	119.38 mm 4.7 in
Pigtail Length	1.5 m 4.921 ft

Optical Specifications

Fiber Type	OM4, LazrSPEED® 550
Insertion Loss, typical	0.4 dB
Return Loss, minimum	20 dB

Environmental Specifications

Safety Standard UL

Packaging and Weights

Packaging quantity 1

Regulatory Compliance/Certifications


Agency **Classification**

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

Included Products

700207012 – LazrSPEED® SC Multiport Shuttered Adapter, Aqua, Single Pack
MFA-SC06-AQ-SHUTTERED

700207012 | MFA-SC06-AQ-SHUTTERED



LazrSPEED® SC Multiport Shuttered Adapter, Aqua, Single Pack

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber adapter
Product Brand	LazrSPEED®
Product Series	MFA

General Specifications

Body Style	Ganged
Color	Aqua
Interface	SC/UPC
Mounting	No flange
Shuttered	Yes
Total Ports, quantity	6

Material Specifications

Alignment Sleeve Material	Zirconia (ceramic)
----------------------------------	--------------------

Optical Specifications

Fiber Mode	Multimode
-------------------	-----------

Packaging and Weights

Packaging quantity	1
---------------------------	---

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
REACH-SVHC	Compliant as per SVHC revision on www.commscope.com/ProductCompliance
ROHS	Compliant

700207012 | MFA-SC06-AQ-SHUTTERED

UK-ROHS

Compliant

