	8	7	6	5	4		3	2	1	
17	EM PART NO.	DESCRIPTION	QTY. WEIGHT				REV. ZONE	REVISIONS DESCRIPTION	BY	DATE
	1 DSC	DISH TO SMALL CROSSOVER CLAMP	1 3.41 LBS				A ZONE	INITIAL RELEASE		02/29/00
	2 SC-P10	SMALL DISH CLAMP HALF	1 1.20 LBS				В	REDRAWN & REVISED	JTS 0	04/09/01
	3 DC-P10	MEDIUM CLAMP HALF	1 2.21 LBS							
		5/8" X 8" GALV THREADED ROD	2 0.64 LBS							
n		1/2" X 6" GALV THREADED ROD	2 0.33 LBS							
		1/2" GALV FLAT WASHER (A325)	4 0.02 LBS							1
		1/2" GALV HEX NUT (A325)	4 0.08 LBS							
		1/2" GALV LOCK WASHER	4 0.01 LBS							
		5/8" GALV FLAT WASHER (A325)	4 0.03 LBS				<u>(6)</u> 7)	(8)		
		5/8" GALV HEX NUT (A325)	4 0.08 LBS							
		5/8" GALV LOCK WASHER	4 0.00 LBS							
	11 GVV-LU3	3/8 GALV LOCK WASHER	4 0.01 Lb3							
						\mathcal{A}	2			
						\overline{A}	2			
				(5)			/)	
Ų.										
				<		>				
				(1)						
							A			
→										-
							\times			
							\times			
							<u> </u>	(10)(11)		
D									//))	T
D					/					
								4)		
	/			\\		$\langle \ \ $	\rightarrow			
				// //						
							PIPES	ARE SOLD SEPERATLY		
					(3)—		ϕ 2-1	ARE SOLD SEPERATLY 1/2" TO Ø 3-1/2" OD PIPE		
							A			
							V			
			PIPES ARE SOLD S	SEPERATLY /						
			PIPES ARE SOLD S \emptyset 2-3/8" TO \emptyset 5"	OD PIPE —						
_							DRAWN BY: SHEET:	DEC. HARPER		
Н		\bigcup			These drawings and specificati property of ANDREW CORPORA only for the specific purpose Andrew Corp	tions are the proprietary ATION and may be used authorized in writing by		of 1 CC-2I5-6		
	NOTEC				ALL DIMENSIONS ARE IN INCHES		CHECKED BY: SCALE: TP NTS	DESCRIPTION: CROSSOVER CLAMP		
	NOTES:		1/0" 0 0	אורר	TOLERANCES UNLESS OTHERWISE		DATE: MATERIAL:	DRAWING TYPE:		
	1. J <u>C</u>	OINS ϕ 2-1/2" O.D. TO ϕ 3-O ϕ 2-3/8" O.D. TO 5" O.D	1/2 U.D. F	117E	$.XX = \pm .03$ FF	FRACTIONS $\pm 1/3$	REVISION: FINISH:			
		$\cup \ \ \varphi 2 - 3/8 \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \ \$	J. PIPE.		.XXX= ± .010 REMOVE BURRS AND BREAK ED	EDGES .005	B GALV	V A123	ORLAND PARK, IL	L. 60462
					DO NOT SCALE THIS			P LBS ANDREW	$7_{ { m ext{@}}}$ U.S.A.	
	8	7	6	5	4		3	2	1	