

# FGS-HTBK-6-5

---



## FiberGuide® 6in Horizontal Tool-less Bracket Kit for 2x6, 4x4 and 4x6in Systems

This 6in bracket attaches to 6in ladder rack using our tool-less Quick Knobs. Used to mount and support 2x6, 4x4 and 4x6in FiberGuide® above ladder racking.

### Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Support mounting kit
<b>Product Brand</b>	FiberGuide®
<b>Product Series</b>	FGS

### General Specifications

<b>Color</b>	Black
<b>Note</b>	Includes fastening hardware
<b>Orientation</b>	Horizontal
<b>Section Type</b>	Bracket

### Dimensions

<b>Height</b>	171.45 mm   6.75 in
<b>Width</b>	114.3 mm   4.5 in
<b>Length</b>	156.21 mm   6.15 in
<b>System Dimensions</b>	102 mm x 102 mm (4 in x 4 in)   102 mm x 152 mm (4 in x 6 in)   51 mm x 152 mm (2 in x 6 in)

### Packaging and Weights

<b>Packaging quantity</b>	1
<b>Weight, net</b>	0.816 kg   1.8 lb

### Included Products

HDW-12021 - FiberGuide® Quick Knob with T-Bolt

# HDW-12021

---



## FiberGuide® Quick Knob with T-Bolt

### Product Classification

<b>Regional Availability</b>	Asia   Australia/New Zealand   EMEA   Latin America   North America
<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Fiber raceway hardware
<b>Product Brand</b>	FiberGuide®
<b>Product Series</b>	FGS
<b>Minimum Order Quantity</b>	10

### General Specifications

<b>Color</b>	Black
<b>Orientation</b>	Horizontal
<b>Section Type</b>	Accessory

### Dimensions

<b>System Dimensions</b>	102 mm x 102 mm (4 in x 4 in)   102 mm x 152 mm (4 in x 6 in)   102 mm x 305 mm (4 in x 12 in)   102 mm x 610 mm (4 in x 24 in)   51 mm x 152 mm (2 in x 6 in)
--------------------------	--

### Environmental Specifications

<b>Flammability Rating</b>	CSA S143   UL 2024   UL 94 V-0
<b>Halogen Characteristics</b>	Blue Angel   TCO '99   WEEE
<b>Safety Standard</b>	CSA   UL

### Packaging and Weights

<b>Packaging quantity</b>	1
<b>Weight, net</b>	0.015 kg   0.033 lb

### Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

# HDW-12021

---

CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

