

# SSC-760233122E6 | 18 in Pole Top for Ericsson 8863 C-Band and 4G



## Top of Pole 18in Dia Concealment Enclosure for C-Band and power supply

- Orderable to mount multi-band and multi-port antennas from multiple antenna vendors
- Variable pole diameter mounting kits available to mount to existing structures

Pole Top Concealment that can accommodate most antenna manufacturers antennas. Please reach out to your CommScope Representative for exact model number.

Mounts directly to CommScope poles with no additional mounting materials. Mounts to other wood and metal poles with separately purchased mounts.

Supports Ericsson C-Band 8863 with 6302 power supply  
Coming support of Samsung RT8808 and Delta 2.0 power supply with additional kit  
Coming support of 4415/4426/4478 with additional kit

-Supports "V4S4SSP-360S-F2" and "NNV4SSP-360S-F2" antenna with separately ordered "860664552" bracket

## Product Classification

<b>Portfolio</b>	CommScope®
<b>Product Type</b>	Pole top
<b>Product Brand</b>	Metro Cell
<b>Ordering Note</b>	CommScope® standard product with terms
<b>Warranty</b>	One year

## General Specifications

<b>Antenna Compatibility, CommScope</b>	CommScope Canister Antennas
<b>Antenna Compatibility, Other Vendors</b>	ACE   AMPHENOL   GALTRONICS   GAMMA NU   JMA   KATHREIN   KMW   ROSENBERGER
<b>Antennas Included</b>	None
<b>Color</b>	Light Gray (RAL 7035)
<b>Color Options</b>	Beige-Grey (RAL 7006)   Black (RAL 9005)   Brown (RAL 8014)   Faux Concrete   Green (RAL 6005)   Metallic Silver   Umbra Grey (RAL 7022)
<b>Cooling</b>	Passive Cooling
<b>Mounting Options</b>	Concrete poles   Fluted poles   Metal poles   Non-tapered poles   Tapered poles   Wood poles
<b>Power Supply Compatibility</b>	6302   ABB CC1600   DELTA 2.0   PSU-AC-08

# SSC-760233122E6 | 18 in Pole Top for Ericsson 8863 C-Band and 4G

**Radio Compatibility, Ericsson** 4415 | 4426 | 4478 | 8863

**Radio Compatibility Samsung** RT8808-77A

**Radios Included** None

## Dimensions

**Height** 812.8 mm | 32 in

**Width** 457.2 mm | 18 in

**Depth** 457.2 mm | 18 in

**Mounting Bolt Circle Diameter** 142.748 mm | 5.62 in | 241.3 mm | 9.5 in

## Ordering Tree



ANTENNA COMPATIBILITY			
3	ACE ACOM-2F15D-14P	5	CommScope 3X-V65S-C3-1XR
3	ACE ACOM-2F15D-18P	3	CommScope NNV4SSP-360S-F4
3	ACE ACOM-2F15D-12P-R2	3	CommScope NNV4SSP-360S-F4-V4
3	Amphenol 2C2U3MT360X06FxyS0	1	CommScope NNVVSSP-360S-FM
3	Amphenol 2C4U3MT360X06FxyS0	1	CommScope V4SSPP-360S-F
3	Amphenol 4U4MT360X06FxyS0	1	CommScope VVSSP-360S-M
3	Amphenol C2U3MT360X06FxyS0	5	CommScope VVSSP-360S-F
3	Amphenol C2U3MT360X12FxyS0	1	CommScope VVSSP-360S-M-V4
3	Amphenol CUT360X06FxyZ0	5	CommScope VVSSP-65S-R1B
3	Amphenol CUUB070X06FxyZ0	3	JMA CX06OMI236-1C
3	Amphenol CUUT070X06FxyZ0	3	JMA CX14OMI236-1C
3	Amphenol CUUT070X12FxyZ0	3	JMA CX16OMI236-1C
3	Amphenol CUUT360X06F54Z0	6	Kathrein 80010745
4	Galtronics GQ2410 Series	6	Kathrein 80010746
3	Galtronics GQ2418 Series	6	Kathrein 84010555
3	Galtronics GQ2412-06613	6	Kathrein 84010556
3	Galtronics GQ2418-06941	6	Kathrein 84010557
3	Galtronics GQ2414-06790	6	Kathrein 84010558
3	Galtronics GQ2414-06939	6	Kathrein 80010783
3	Gamma Nu DOYZ9X360F14	6	Kathrein 80010784
3	Gamma Nu DOYZ9X360F12	2	Kathrein 84010603
5	Gamma Nu OYZ9X360F10	2	Kathrein 84010604
4	Gamma Nu OYZ9X180V10-RET	6	KMW FX-OM2L10H2
4	Gamma Nu OYZ9X360V10T20-RET	4	ROSENBERGER
4	Gamma Nu QOYZ9X360F14T6		CA-OIOITJTJVEJX360F-JS06
5	Gamma Nu OYZ9X360F10		

ANTENNA COLOR	
1	Light Grey (RAL 7035)
2	Green (RAL 6005)
3	Black (RAL 9005)
4	Brown (RAL 8014)
5	Beige Grey (RAL 7006)
6	Fairfax Brown (SW 2856)
8	Federal Park Brown
9	Metallic Silver
20	Umbra Grey (RAL 7022)
C	Faux Concrete
F	Signal Black (RAL 9004)
G	Black Green (RAL 6012)
W	White (RAL 9010)
Z	Antique Bronze (SRSL 45893)

## Material Specifications

**Finish Aluminum** Chromate

**Finish Concealment Covers** Powder coated

**Material Type** Aluminum | Steel

## Environmental Specifications

# SSC-760233122E6 | 18 in Pole Top for Ericsson 8863 C-Band and 4G

---

**Thermal Compliance** GR-487

## Packaging and Weights

**Volume** 0.134 m<sup>3</sup> | 4.72 ft<sup>3</sup>

**Weight (unloaded)** 34.019 kg | 75 lb

## \* Footnotes

**Warranty** For more information, please consult our Product Warranty guidelines