


FOSC-SPLICE-TRAYS

Base Product



FOSC® Splice Tray

- FOSC splice trays hinged for access to any splice without disturbing other trays
- The FOSC splice tray portfolio includes versions for storing single and/or ribbon (mass) fusion splices, ribbon splices with ribbon slack on the same tray, and patching capabilities

FOSC splicing trays store fibers and splices in FOSC splice closures and any network element such as fiber panels that accepts FOSC trays. In all parts of the tray, the arrangement of fiber and splices conforms to minimum bend radius requirements.

The trays' hinged feature provides fiber protection as well as easy access. Storage baskets are available for slack storage of extra or uncut fiber lengths.

Product Classification

Regional Availability	Asia Australia/New Zealand EMEA Latin America North America
Portfolio	CommScope®
Product Type	Fiber splice tray
Product Brand	FOSC®
Product Series	FOSC 100 FOSC 400 FOSC 450 FOSC 600

General Specifications

Application	For use with FOSC-100 Fiber closures For use with FOSC-400A Fiber closures For use with FOSC-400B Fiber closures For use with FOSC-400D Fiber closures For use with FOSC-450 Fiber closures For use with FOSC-600 Fiber closures
Color	Gray
Splicing Type	Heat shrink Mass fusion, ribbon

Ordering Tree

FOSC - A - TRAY - XXX - 1

Splice protectors at tray exterior

S24	24 SMOUV splice protectors (45mm)
A24	24 ANT splice protectors
4R4	4 splice protectors for ribbon cable with 4 fibers

OR

Splices in modules at tray interior¹

12	12 splice protectors 2 modules, 6 splices/module
24	24 splice protectors 2 modules, 12 splices/module

¹ SMOUV modules in these trays can be removed and replaced by a different style splice protector.

FOSC-SPLICE-TRAYS

FOSC - B - TRAY - XXX - 1

Splice protectors at tray exterior

S12	12 SMOUV splice protectors (45mm)
S24	24 SMOUV splice protectors (45mm)
424	24 ANT splice protectors
6R4	6 splice protectors for ribbon cable with 4 fibers

OR

Splices in modules at tray interior¹

12	12 splice protectors 2 modules, 6 splices/module
24	24 splice protectors 2 modules, 12 splices/module

¹ SMOUV modules in these trays can be removed and replaced by a different style splice protector.

FOSC - D - TRAY - XXXX - 1

Splices in modules at tray interior¹

36	36 splice protectors, 6 modules, 6 splices/module
S96	96 SMOUV splice protectors (45 mm)
L96	96 SMOUV splice protectors (60 mm)
A96	96 ANT splice protectors
RT24	24 splices for ribbon cable with 12 fibers 4 modules, 6 splices/module

¹ SMOUV modules in these trays can be removed and replaced by a different style splice protector.

Catalog Number

FOSC-ACC-__-TRAY-__-__

Closure Size

A*
B
C
D

Choose Option	Tray Size	Capacity Single	Mass Fusion (12 Fiber Ribbon)
12	A, B	12	72
24	A, B	24	N/A
12	C	12	144
24	C	24	N/A
36	C	36	N/A
00	D	N/A	N/A
36	D	36	432
48	D	48	N/A
72	D	72	N/A
96**	D	96	N/A

* Choose this option for the BS closure as well

** FIST style modules, add -S60 to end of the description)

Environmental Specifications

Environmental Space Indoor | Outdoor

Packaging and Weights

Packaging quantity 1

Packaging Type Bag | Carton

FOSC-SPLICE-TRAYS
