


## HELIAX® PIM Guard Applications

PIM Guard Accessories, reduce the PIM where it matters most, the Hi-Risk PIM zone exists in close proximity to the antenna; in front, above, below, and even behind it. The zone is defined as:

- 10' (3M) directly above or below the antenna
- 5' (1.5M) behind the antenna
- 100' (30M) in front of the antenna



**Mounting to Round Member for cable support**  
Material ID: PGP-CS04, PGP-CS08, PGP-CS10, PGP-CS12, PGP-CS16, SA-3C, SA-1C, RA-38C, UHA-3C, FBR-COIL-S

**Supporting Fiber / Power / Coax cables**  
Material ID: SSH-411, SSH-1117, SSH-1014, SSH-1416, SSH-47, SSH-710, SWH-200-10, SA-ISO

**Mounting to Angle Iron for cable support**  
Material ID: UA-3C, SA-3C, RA-38C, UHA-3C, FBR-COIL-S

## SnapTak Adjustable Hangers



Material ID:	Description:	Application:	Use with:
<a href="#">SSH-411</a> , <a href="#">SSH-1117</a> , <a href="#">SSH-1014</a> , <a href="#">SSH-1416</a> , <a href="#">SSH-47</a> , <a href="#">SSH-710</a>	Polymer Snap-in Adjustable Hangers	Support cables from 4.0mm to 17.0mm in diameter.	3/4" stamped holes, PGP-CS04, PGP-CS08, PGP-CS10, PGP-CS12, PGP-CS16, UA-3C, SA-3C, SA-1TR, SA-1C, RA-38C, UHA-3C

[Installation Bulletin:](#)



## SnapWrap Adjustable Hanger



Material ID:	Description:	Application:	Use with:
<a href="#">SWH-200-10</a>	Polymer Snap-in Adjustable Wrap Hanger	Bundle multiple cable types and sizes into a 1/2" (12.7mm) to 2" (50.8mm) bundle.	3/4" stamped holes, PGP-CS04, PGP-CS08, PGP-CS10, PGP-CS12, PGP-CS16, UA-3C, SA-3C, SA-1TR, SA-1C, RA-38C, UHA-3C

[Installation Bulletin:](#)



## Cable Support Brackets



Material ID:	Description:	Application:	Use with:
<a href="#">PGP-CS04</a> , <a href="#">PGP-CS08</a> , <a href="#">PGP-CS10</a> , <a href="#">PGP-CS12</a> , <a href="#">PGP-CS16</a>	Polymer 4 to 16 position cable support brackets	Antenna and RRU cable support brackets accommodate 8 to 32 cables. Up to 2 stackable hangers per position.	All SnapStak and SnapTak hangers, SWH-200-10



## Angle Adapter




Material ID:	Description:	Application:	Use with:
<a href="#">UA-3C</a>	Polymer two hole angle adapter	Angle member attachment. Includes torque stop set bolt to ensure proper attachment force. Two 3/4" holes for Snap-in style hangers.	All SnapStak and SnapTak hangers, SWH-200-10


[Installation Bulletin:](#)




## Standoff Adapters




Material ID:	Description:	Application:	Use with:
<a href="#">SA-3C</a>	Polymer three hole standoff adapter	Two sets of slots for round member attachment. 3/8" holes for bolt down attachment. Three 3/4" holes for Snap-in style hangers.	All SnapTak hangers, MCLICK Hangers, SWH-200-10




[Installation Bulletin:](#)




Material ID:	Description:	Application:	Use with:
<a href="#">SA-1TR</a>	Polymer multi-function one hole standoff adapter	Snaps into 3/4" holes or threads into 3/8" & 1/2" bolts & U-bolts. One 3/4" hole for Snap-in style hangers.	All SnapTak hangers, MCLICK hangers, SWH-200-10




[Installation Bulletin:](#)




Material ID:	Description:	Application:	Use with:
<a href="#">SA-1C</a>	Polymer one hole standoff adapter	Round member attachment. One 3/4" hole for Snap-in style hangers.	All SnapTak hangers, SWH-200-10




[Installation Bulletin:](#)




Material ID:	Description:	Application:	Use with:
<a href="#">RA-38C</a>	Polymer multifunction one hole standoff adapter	Round member or angle member attachment. 3/8" holes for bolt down attachment. One 3/4" hole for Snap-in style hangers.	All SnapTak hangers, MCLICK hangers, SWH-200-10



[Installation Bulletin:](#)




Material ID:	Description:	Application:	Use with:
<a href="#">UHA-3C</a>	Polymer universal three hole standoff adapter	Round member or angle member attachment. Three 3/4" holes for snap-in hangers, or locations to mount three grommets or has a 3/8" holes for threaded rod attachment.	All SnapTak hangers, MCLICK hangers, cable grommets, SWH-200-10




[Installation Bulletin:](#)

## SnapStak Isolator




Material ID:	Description:	Application:	Use with:
<a href="#">SA-ISO</a>	Polymer one hole isolator for Snap-in Adjustable Hangers	Snaps in between hanger and mounting surface, and between stacked hangers to remove metal to metal contact.	3/4" stamped holes, all SnapStak hangers




[Installation Bulletin:](#)

## Excess Cable Management



Material ID:	Description:	Application:	Use with:
<a href="#">FBR-COIL-S</a>	Engineered plastic fiber coiling reel	Round member or angle member attachment. Accommodates 16' (5M) of excess 7mm fiber.	5-7mm fiber cables



[Installation Bulletin:](#)

### CommScope

1100 CommScope Place SE P.O. Box 339, Hickory, NC 28603-0339  
 (828) 324-2200 (800) 982-1708  
[www.commscope.com](http://www.commscope.com)

### Technical Support

+1 888 297 6433, Option 3 (Toll Free US and Canada)  
 +1 828 323 4220, Option 3 (local)  
<https://www.commscope.com/wisupport> (open a ticket)

Notice: CommScope disclaims any liability or responsibility for the results of improper or unsafe installation, inspection, maintenance, or removal practices.  
 Aviso: CommScope no acepta ninguna obligación ni responsabilidad como resultado de prácticas incorrectas o peligrosas de instalación, inspección, mantenimiento o retiro.  
 Avis : CommScope décline toute responsabilité pour les conséquences de procédures d'installation, d'inspection, d'entretien ou de retrait incorrectes ou dangereuses.  
 Hinweis: CommScope lehnt jede Haftung oder Verantwortung für Schäden ab, die aufgrund unsachgemäßer Installation, Überprüfung, Wartung oder Demontage auftreten.  
 Atenção: A CommScope abdica do direito de toda responsabilidade pelos resultados de práticas inadequadas e sem segurança de instalação, inspeção, manutenção ou remoção.  
 Avvertenza: CommScope declina eventuali responsabilità derivanti dall'esecuzione di procedure di installazione, ispezione, manutenzione e smontaggio improprie o poco sicure.  
 注意: CommScope 公司申明對於不恰當或不安全的安裝、檢驗、維修或拆卸操作所導致的後果不負責任 何義務和責任

© 2023 CommScope