


# UGBKIT-0412

---



Copper Ground Buss Bar, 1/4 in x 4 in x 12 in (6.4 mm x 101.6 mm x 304.8 mm)

## Product Classification

<b>Product Type</b>	Grounding bar
<b>Product Brand</b>	HELIX®
<b>Ordering Note</b>	CommScope® standard product (Global)

## Dimensions

<b>Height</b>	101.6 mm   4 in
<b>Length</b>	304.8 mm   12 in
<b>Material Thickness</b>	6.35 mm   0.25 in
<b>Hole Size</b>	7/16 in   7/16 in x 5/8 in
<b>Hole Distance, center to center</b>	19.05 mm   0.75 in

## Material Specifications

<b>Material Type</b>	Copper
----------------------	--------

## Packaging and Weights

<b>Height, packed</b>	454.66 mm   17.9 in
<b>Width, packed</b>	248.92 mm   9.8 in
<b>Length, packed</b>	50.8 mm   2 in
<b>Included</b>	Galvanized angle adapter   Grounding bar   Insulators   Mounting brackets   Universal hardware
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	3.36 kg   7.408 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

# UGBKIT-0412

---

REACH-SVHC	Compliant as per SVHC revision on <a href="http://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant



## Included Products

GB-HK-DPU	- Universal Buss Bar Installation Hardware Kit, UL467 Compliant
-----------	---

# GB-HK-DPU

---



## Universal Buss Bar Installation Hardware Kit, UL467 Compliant

### Product Classification

<b>Product Type</b>	Attachment kit
<b>Product Brand</b>	HELIAX®
<b>Ordering Note</b>	CommScope® standard product in the United States and Canada

### General Specifications

<b>Accessories</b>	Grounding Bars
--------------------	----------------

### Packaging and Weights

<b>Height, packed</b>	170.18 mm   6.7 in
<b>Width, packed</b>	129.54 mm   5.1 in
<b>Length, packed</b>	99.06 mm   3.9 in
<b>Included</b>	Angle adapters   Drive pin anchor   Insulators, Mounting brackets   Universal hardware
<b>Packaging quantity</b>	1
<b>Weight, gross</b>	2.6 kg   5.732 lb

### Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
CHINA-ROHS	Below maximum concentration value
REACH-SVHC	Compliant as per SVHC revision on <a href="https://www.commscope.com/ProductCompliance">www.commscope.com/ProductCompliance</a>
ROHS	Compliant
UK-ROHS	Compliant

