## FD4S-B288S00JBB2



FDH 4000, 288 distribution fibers, no splitters loaded, LC/APC, dielectric, loose tube, 100 ft stub, distribution cable all 144f stub and input cable 24 fiber

- Thermoplastic construction provides UV stabilization, flame retardancy, and chemical & impact resistance
- Provides air/water tight seal ensuring protection from flooding and fungus
- Unsurpassed reliability makes it ideal for aerial and below grade applications
- Supports diverse Plug-and-Play splitter and xWDM module Configurations

#### **Product Classification**

Regional Availability

Asia | Australia/New Zealand | EMEA | Latin America | North America

**Product Type** Fiber distribution closure

Product Series FDH 4000

### General Specifications

**Access** Front

Cable Type Dielectric - Stranded

**Color** Black

**Distribution Cables, quantity** 2

Fibers per Distribution Cable, quantity 144

Fibers per Feeder Cable, quantity 24

Interface, Input LC

Interface Feature, Input APC

Mounting Handhole | Pole | Wall

Splitter Slots, quantity 9

### Dimensions

 Height
 812.8 mm | 32 in

 Width
 241.3 mm | 9.5 in


 Cable Length
 30.48 m | 100 ft


Enclosure Size Small


## Dimension Drawing



# FD4S-B288S00JBB2








Ordering Tree

# FD4S-B288S00JBB2



## **Environmental Specifications**

Environmental Space Above ground | Aerial | Below ground

Qualification Standards | IEC 60529, IP68 | Telcordia GR-3121-CORE | Telcordia GR-3125-CORE

Packaging and Weights

Packaging quantity

Packaging Type Pallet

**Weight, net** 15.876 kg | 35 lb

### Regulatory Compliance/Certifications

### Agency Classification

CHINA-ROHS Above maximum concentration value

ROHS Compliant/Exempted UK-ROHS Compliant/Exempted



**COMMSCOPE®**