ConQuest® Cable in Conduit, 13 mm, SDR 11, terracotta (F677TSEF XP)



 *Product complies with the Build America, Buy America Act (BABAA) requirements of the Infrastructure Investment and Jobs Act of 2021 (Pub. L. 117- 58, §§ 70901-70953), or is the subject of a waiver approved by the Secretary of Commerce or designee. Compliance requirements and waiver applicability vary based on government funding program. Check the laws and regulations for your specific program.

Product Classification

Regional Availability	North America
Product Type	Coaxial cable-in-conduit
Product Brand	ConQuest®
Product Series	6 Series
Government Funding	Build America Buy America (BABA) compliant*

General Specifications

Cable Type	Series 6
Cable-In-Conduit Type	Drop in duct
Color	Terracotta
Conduit Type	Non-toneable
Wall Type	Smooth
Dimensions	
Length	304.8 m 1000 ft

SDR 11
13 mm

Packaging and Weights

Weight, net

107.148 kg/km | 72 lb/kft

Included Products

4842903 F677TSEF XP (830BMU) XPRESSPREP® Coaxial Drop Cable, 75 Ohm, Series 6, black PE jacket, flooded for underground

Page 1 of 5

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: April 11, 2024



XPRESSPREP® Coaxial Drop Cable, 75 Ohm, Series 6, black PE jacket, flooded for underground



Product Classification

Product Type	Coaxial drop cable
Product Brand	XPRESSPREP®
Product Series	6 Series
Warranty	One year
General Specifications	
Cable Type	Series 6
Center Conductor Type	Solid
Jacket Color	Black
Jacket Marking	Feet
Performance Note	Attenuation listed represents maximum values at standard condition of 20 $^\circ\mathrm{C}$ (68 $^\circ\mathrm{F})$
Shield Construction Type	Trishield
Dimensions	
Diameter Over Center Conductor, nominal	1.016 mm 0.04 in
Diameter Over Dielectric, nominal	4.572 mm 0.18 in
Diameter Over Inner Shield (Tape), nominal	4.75 mm 0.187 in
Diameter Over Jacket, nominal	7.061 mm 0.278 in
Jacket Thickness, nominal	0.762 mm 0.03 in
Center Conductor Gauge	18 AWG
Inner Shield (Braid) Gauge	34 AWG
Electrical Specifications	
Capacitance	53.15 pF/m 16.2 pF/ft

Page 2 of 5

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 1, 2023



Characteristic Impedance	75 ohm
Characteristic Impedance Tolerance	±3 ohm
dc Resistance Note	Nominal values based on a standard condition of 20 °C (68 °F)
dc Resistance, Inner Conductor, nominal	100.066 ohms/km 30.5 ohms/kft
dc Resistance, Loop, nominal	121.063 ohms/km 36.9 ohms/kft
dc Resistance, Outer Conductor, nominal	20.997 ohms/km 6.4 ohms/kft
Nominal Velocity of Propagation (NVP)	85 %
Operating Frequency Band	5–3000 MHz
Structural Return Loss, Grade A	≥15 dB @ 1801-3000 MHz ≥20 dB @ 5-1800 MHz
Structural Return Loss, Grade C	≥15 dB @ 1801−3000 MHz ≥20 dB @ 1002−1800 MHz ≥23 dB @ 5− 1002 MHz
Structural Return Loss, Grade G	≥15 dB @ 1801−3000 MHz ≥20 dB @ 1002−1800 MHz ≥26 dB @ 5− 1002 MHz

Attenuation

Frequency (MHz)	Attenuation (dB/100 m)	Attenuation (dB/100 ft)
5.0	1.9	0.58
55.0	5.25	1.6
83.0	б.4	1.95
85.0	6.46	1.97
187.0	9.35	2.85
204.0	9.84	3
211.0	10	3.05
250.0	10.82	3.3
300.0	11.64	3.55
350.0	12.63	3.85
400.0	13.61	4.15
450.0	14.43	4.4
500.0	15.29	4.66
550.0	16.08	4.9
600.0	16.73	5.1
750.0	18.54	5.65
865.0	20.01	6.1
1000.0	21.49	6.55
1218.0	23.66	7.21

Page 3 of 5

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 1, 2023



24.71	7.53
25.71	7.84
26.68	8.13
27.63	8.42
28.54	8.7
29.39	8.96
29.44	8.97
31.17	9.5
32.83	10.01
35.2	10.73
37.46	11.42
38.91	11.86
	25.71 26.68 27.63 28.54 29.39 29.44 31.17 32.83 35.2 37.46

Material Specifications

Center Conductor Material	Copper-clad steel
Dielectric Material	Foam PE
Jacket Material	PE
Inner Shield (Braid) Coverage	77 %
Inner Shield (Braid) Material	Aluminum
Inner Shield (Tape) Material	Aluminum/Polymer/Aluminum (APA) bonded
Outer Shield (Tape) Material	Aluminum/Polymer/Aluminum (APA) bonded

Environmental Specifications

Corrosion Protection	Migraheal®
Environmental Space	Buried (Network Powered)
Flame Test Listing	BMU NEC Article 830

Packaging and Weights

Packaging Type

Weight, gross

Reel 49.109 kg/km | 33 lb/kft

Regulatory Compliance/Certifications

Agency	Classification
CHINA-ROHS	Below maximum concentration value
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

Page 4 of 5

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 1, 2023

COMMSCOPE°

REACH-SVHC

ROHS

UK-ROHS



Compliant as per SVHC revision on www.commscope.com/ProductCompliance

Compliant Compliant

Page 5 of 5

©2024 CommScope, Inc. All rights reserved. CommScope and the CommScope logo are registered trademarks of CommScope and/or its affiliates in the U.S. and other countries. For additional trademark information see https://www.commscope.com/trademarks. All product names, trademarks and registered trademarks are property of their respective owners. Revised: September 1, 2023

