

Standard Grounding Kit for 1/2 in corrugated coaxial cable and elliptical waveguide 180 and 220

#### **Product Classification**

**Product Type** Grounding kit

Ordering Note CommScope® standard product (Global)

General Specifications

Bonding Conductor Jacketing MaterialPVCBonding Conductor MaterialCopperBonding Conductor Wire Size6 gauge

Cable Type Corrugated | Elliptical waveguide

**Color** Black

**Grounding Kit Type** Standard Grounding Kits

Grounding Strap Material Copper

**Lug Attachment** Factory attached

**Lug Type** Two-hole lug

Thread Size 3/8 in

**Dimensions** 

Bonding Conductor Length609.6 mm | 24 inCable Jacketing Removal Length, maximum58.42 mm | 2.3 inCable Jacketing Removal Length, minimum55.88 mm | 2.2 inCompatible Diameter, maximum16.51 mm | 0.65 inCompatible Diameter, minimum15.494 mm | 0.61 in

Nominal Size 1/2 in

**Waveguide Size** WR42 | WG20 | R220 | WR51 | WG19 | R180

**Electrical Specifications** 

Current Handling Tested to withstand 100,000 amps peak current surge

Current Handling Test Method MIL-STD-1757

**COMMSCOPE®** 

**Grounding, Bonding and Shielding Test Method**MIL-STD-188-124A

**Lightning Protection Test Method**IEC 1024-1

Material Specifications

Rivet Material Copper

**Environmental Specifications** 

**Operating Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +85 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +185 \,^{\circ}\text{F})$ 

**Storage Temperature**  $-40 \,^{\circ}\text{C} \text{ to } +80 \,^{\circ}\text{C} \, (-40 \,^{\circ}\text{F to } +176 \,^{\circ}\text{F})$ 

**Blowing Rain Test Method** MIL-STD-810, Method 506

**Corrosion Test Method** MIL-STD-1344, Method 1001

Freezing Rain/Icing Test Method MIL-STD-810, Method 521

**Humidity Test Method** MIL-STD-1344, Method 1002

**Immersion Test Method** IEC 60529:2001, IP68

UV Resistance Test Method MIL-STD-810, Method 505

Vibration Test Method MIL-STD-202, Method 214

Weatherproofing Method Butyl and electric tape

Packaging and Weights

Height, packed 266.7 mm | 10.5 in

**Width, packed** 266.7 mm | 10.5 in

**Length, packed** 58.42 mm | 2.3 in

Included Grounding kit | Hardware | Lug | One roll of 2 in PVC tape | One

roll of 24 in butyl rubber tape

Packaging quantity 1

**Weight, gross** 0.72 kg | 1.587 lb

## Regulatory Compliance/Certifications

Agency Classification

CHINA-ROHS Below maximum concentration value

ISO 9001:2015 Designed, manufactured and/or distributed under this quality management system

REACH-SVHC Compliant as per SVHC revision on www.commscope.com/ProductCompliance

ROHS Compliant UK-ROHS Compliant





### Included Products

42615-10 - Butyl Rubber Tape, 24 in 9905-71 - Black 2 in PVC Tape, 20 ft

## \* Footnotes

**Grounding, Bonding and Shielding Test Method** Military Standard for Grounding, Bonding, and Shielding: Bond Resistance

Requirement of a Maximum dc resistance of 0.001 ohm

**Lightning Protection Test Method**Protection Against Lightning Electromagnetic Impulse, Table 1—Protection

Level III-IV, 1995-02







#### Butyl Rubber Tape, 24 in

Product Classification

**Product Type**Weatherproofing tape

Ordering Note CommScope® non-standard product

General Specifications

**Application** Provides additional moisture seal for cable connections

**Applications per Kit**One 1/2 in-2-1/4 in | One 1/2 in-7/8 in | One 1/2 in-7/8 in to

device | Two 1/2 in-1/2 in

**Color** Black

**Dimensions** 

 Width
 63.5 mm | 2.5 in

 Length
 609.6 mm | 24 in

**Nominal Size** 1-1/4 in | 1-5/8 in | 1/2 in | 1/4 in | 2-1/4 in | 3/8 in | 5/8 in | 7

/8 in

Material Specifications

Material Type Butyl rubber tape

**Environmental Specifications** 

**UV Resistance Test Method**Butyl test method in QUV weatherometer cycle of 8 hours UV at 150 °F then 4

hours of condensation at 104 °F

**UV Resistance, minimum with no degradation** ≥1000 hours

Weather Resistance Test Method 04AS00-03.6.0 | MIL-STD-1344A, Method 1002

Packaging and Weights

 Height, packed
 63.5 mm | 2.5 in

 Width, packed
 71.12 mm | 2.8 in

 Length, packed
 25.4 mm | 1 in

Page 4 of 7



**Packaging quantity** 

1

Weight, gross

0.17 kg | 0.375 lb

## Regulatory Compliance/Certifications

Agency

Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system





### Black 2 in PVC Tape, 20 ft

#### **Product Classification**

**Product Type** Weatherproofing tape

Ordering Note CommScope® non-standard product

General Specifications

**Application** Provides additional moisture seal for cable connections

**Applications per Kit** Four 1/2 in -1/2 in | Four 1/2 in -7/8 in to device | One 1/2 in -2-1/4 in | Two 1/2 in -7/8

in

**Color** Black

**Dimensions** 

 Width
 50.8 mm | 2 in

 Length
 6096 mm | 240 in

**Nominal Size** 1-1/4 in | 1-5/8 in | 1/2 in | 1/4 in | 2-1/4 in | 3/8 in | 5/8 in | 7/8 in

Material Specifications

Material Type PVC tape

## **Environmental Specifications**

**UV Resistance Test Method** PVC tape test method UL 510, ASTM D1000

Weather Resistance Test Method 04AS00-03.6.0 | MIL-STD-1344A, Method 1002

Packaging and Weights

 Height, packed
 63.5 mm | 2.5 in

 Width, packed
 63.5 mm | 2.5 in

 Length, packed
 50.8 mm | 2 in

Packaging quantity 1

**Weight, gross** 0.08 kg | 0.176 lb

Page 6 of 7

## Regulatory Compliance/Certifications

#### Agency

#### Classification

ISO 9001:2015

Designed, manufactured and/or distributed under this quality management system

