

	OTE2	Mini-OTE 200	Mini-OTE 300	Mini-OTE 400
				
<b>Style</b>	Butt + inline	Butt	Butt + inline	Butt
<b>Network location</b>	Aerial*	Aerial Handhole Pedestal	Aerial strand Handhole Pedestal	Aerial Handhole Pedestal
<b># ports (max) &amp; type</b>	16 full size	6 full size or 8 DLX miniaturized	12 full size or 12 DLX miniaturized	8 full size or 8 DLX miniaturized
<b>Feeder cable diameter</b>	7 - 16mm (0.276 - 0.629")	4 - 15mm (0.157 - 0.590")	5.84 - 12.7mm (0.229 - 0.500")	5.5 - 6mm (0.217 - 0.236")
<b>Cable type</b>	Loose tube	Loose tube	Loose tube, flat drop, ribbon, armored	Micro cable
<b>Loop storage</b>	Yes	Yes	Yes	Yes
<b>Branches</b>	6 cables	2 cables of $\varnothing$ 4-9mm or flat ( $\varnothing$ 0.157 - 0.354")	2 flat cables of $\varnothing$ 5.84mm ( $\varnothing$ 0.23" min)	No
<b>Splice capacity</b>	120 (SMOUV 45)	24 (SMOUV 45) or 48 (SMOUV 30)	40 (SMOUV 61)	8 (SMOUV 45)
<b>Dark fiber storage</b>	No extra tray	No extra tray	Extra tray	No extra tray
<b>Passive optical component options</b>				
<b>Splitter</b>	None or 1:4 or 1:8 or 1:16	None or 1:4 or 2x1:4 or 1:8	None or 1:2 or 1:4 or 1:8	None
<b>CCWDM</b>	No	No	2 or 4 or 8 Channel	No
<b>Tap</b>	No	No	2 or 4 or 8	No
<b>Dimensions</b>	357 x 191 x 171mm (14.0 x 7.5 x 6.7")	360 x 166 x 130mm (14.7 x 6.5 x 5.2")	342.9 x 182.9 x 121.9mm (13.5 x 7.2 x 4.8")	155 x 105 x 270mm (6.1 x 4.1 x 10.6")
<b>Grounding</b>	No	No	Yes	No
<b>Color</b>	Gray	Black or gray	Black	Black
<b>Sealing level</b>	IP65	IP68	IP68	IP68
<b>Compliance</b>	IEC	IEC	Telcordia GR-771**	IEC and Telcordia GR-771**

\* Not UL listed for wall mount use in USA

\*\* See CommScope test reports for exceptions