








Pole-top solutions		Middle of pole solutions		Bottom of pole solutions	Integrated pole solutions				
									
12" pole-top	18" pole-top	Radio enclosure pico/micro	Wood pole bracket	PoleCab 26" sq or 30" sq	Integrated straight pole	Integrated pole base			
Application									
Ideal for existing pole deployments in public right-of-way or attachment to replacement poles with or without luminaires		Retrofit virtually any pole, anywhere Flexible solution for existing pole of varying heights and diameters		The ideal choice for high-power radios Radio and all ancillary equipment in easy-to-service location		Ideal in jurisdictions with strict zoning laws. Mount and conceal active antennas equipment utilizing pole modules			
Features and benefits									
<ul style="list-style-type: none"> • Accepts multiple Ericsson Pico radios. • Includes mounting for Raycap OVP • Variable pole mounting kits available • Slimline design for maximum aesthetic value • Accepts multiple antenna models • Patent pending thermal management • GR-487 thermally tested 	<ul style="list-style-type: none"> • Accepts two Nokia Pico radios with mounting for future LAA • Variable pole mounting kits available • Slimline design for maximum aesthetic value • Accepts multiple antenna models • Patent pending thermal management • GR-487 thermally tested 	<ul style="list-style-type: none"> • Accepts wide range of Ericsson and Nokia Pico radios • Highly flexible to include diplexers, splitters, AC disconnect • Mounts to tapered and non-tapered wood or composite poles • Micro version accepts 2 Ericsson RRU11s • Lockable • GR-487 thermally tested 	<ul style="list-style-type: none"> • Available in pico and micro versions • Hides and protects equipment • Zero ground footprint • Multiple mounting options available • Multiple colors available • Available with or without shroud • GR-487 thermally tested 	<ul style="list-style-type: none"> • 26in or 30in Square base accepts low to high-power single or dual band radios • 5G upgradable with expansion placeholder • Ideal for downtown scenarios • Mounts for Ericsson or Nokia radios • Decorative base and antenna mounts with or without luminaires • Multiple pole and Antenna mounting options • Battery backup and power options • Highly flexible configurations • GR-487 thermally tested 	<ul style="list-style-type: none"> • Includes everything needed for a low-power 4G/5G, 4G only or 5G only outdoor small cell site. • 12in Dia radio concealment modules conceal up to 4 low power radios • Pole Top concealment module for 5G or LAA/CBRS radios • GR-487 thermally verified 	<ul style="list-style-type: none"> • Includes everything needed for a low-power 4G/5G outdoor small cell site. • 12in Dia radio concealment modules conceal up to 4 low power radios • Pole top concealment module for LAA/CBRS radio mounting • GR-487 thermally verified 			