



4-port sector antenna, 4x 1710–2180 MHz, 65° HPBW, RET compatible

- Each DualPol® array can be independently adjusted for greater flexibility
- Excellent gain, VSWR, front-to-back ratio, and PIM specifications for robust network performance
- Ideal choice for site collocations and tough zoning restrictions
- Great solution to maximize network coverage and capacity

Electrical Specifications

Frequency Band, MHz	1710–1880	1850–1990	1920–2180
Gain, dBi	17.7	18.0	18.0
Beamwidth, Horizontal, degrees	67	66	64
Beamwidth, Vertical, degrees	7.5	7.0	6.6
Beam Tilt, degrees	0–10	0–10	0–10
USLS (First Lobe), dB	18	18	18
Front-to-Back Ratio at 180°, dB	30	30	30
CPR at Boresight, dB	22	22	21
CPR at Sector, dB	8	9	9
Isolation, Cross Polarization, dB	30	30	30
VSWR Return Loss, dB	1.4 15.6	1.4 15.6	1.4 15.6
PIM, 3rd Order, 2 x 20 W, dBc	-153	-153	-153
Input Power per Port, maximum, watts	350	350	350
Polarization	±45°	±45°	±45°
Impedance	50 ohm	50 ohm	50 ohm

Electrical Specifications, BASTA*

Frequency Band, MHz	1710–1880	1850–1990	1920–2180
Gain by all Beam Tilts, average, dBi	17.2	17.2	17.5
Gain by all Beam Tilts Tolerance, dB	±0.3	±0.3	±0.5
Gain by Beam Tilt, average, dBi	0 ° 17.0 5 ° 17.3 10 ° 17.0	0 ° 17.1 5 ° 17.4 10 ° 17.0	0 ° 17.4 5 ° 17.7 10 ° 17.2
Beamwidth, Horizontal Tolerance, degrees	±2.7	±2.3	±3.5
Beamwidth, Vertical Tolerance, degrees	±0.5	±0.4	±0.4
USLS, beampeak to 20° above beampeak, dB	18	19	19
Front-to-Back Total Power at 180° ± 30°, dB	26	26	26
CPR at Boresight, dB	22	22	22
CPR at Sector, dB	9	9	9

* CommScope® supports NGMN recommendations on Base Station Antenna Standards (BASTA). To learn more about the benefits of BASTA, [download the whitepaper Time to Raise the Bar on BSAs.](#)

Array Layout

General Specifications

Operating Frequency Band	1710 – 2180 MHz
Antenna Type	Sector
Band	Single band
Performance Note	Outdoor usage

Mechanical Specifications

RF Connector Quantity, total	4
RF Connector Quantity, high band	4
RF Connector Interface	7-16 DIN Female
Color	Light gray
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Radiator Material	Low loss circuit board
Radome Material	PVC, UV resistant
RF Connector Location	Bottom
Wind Loading, frontal	419.0 N @ 150 km/h 94.4 lbf @ 150 km/h
Wind Loading, lateral	113.0 N @ 150 km/h 25.4 lbf @ 150 km/h
Wind Speed, maximum	241 km/h 150 mph

Dimensions

Length	1297.0 mm 51.1 in
Width	305.0 mm 12.0 in
Depth	166.0 mm 6.5 in
Net Weight, without mounting kit	13.9 kg 30.6 lb

Remote Electrical Tilt (RET) Information

Model with Factory Installed AISG 2.0 Actuator HBXX-6516DS-A2M

Packed Dimensions

Length	1427.0 mm 56.2 in
Width	402.0 mm 15.8 in
Depth	292.0 mm 11.5 in
Shipping Weight	23.5 kg 51.8 lb

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

CE

Classification

Compliant by Exemption

Designed, manufactured and/or distributed under this quality management system

Above Maximum Concentration Value (MCV)

Compliant with the relevant CE product directives



Included Products

600899A-2 — Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

* Footnotes

Performance Note

Severe environmental conditions may degrade optimum performance