

# R2V4PX310R



12-port sector antenna, 4x 698–960 and 8x 1710–2690 MHz, 65° HPBW, 6x RET with manual override. Bands cascaded SRET (Antenna 1 and Antenna 2).

- Integrated Internal Remote Electrical Tilt (RET), with independent control of electrical tilt with manual override on all arrays
- All Internal RET actuators are connected in “Cascaded SRET” configuration

## OBSOLETE

This product was discontinued on: **December 31, 2018**

### Replaced By

RRV4-65D-R6	12-port sector antenna, 4x 694–960 and 8x 1695–2690 MHz, 65° HPBW, 6x RET. Antenna rear wind loading 880N @ 150km/h
RRV3-65D-R5	10-port sector antenna, 4x 694–960 and 6x 1695–2690 MHz, 65° HPBW, 5x RET

## Electrical Specifications

Frequency Band, MHz	698–790	790–890	890–960	1710–1920	1920–2170	2300–2690
Gain, dBi	16.0	16.6	16.9	16.4	17.7	18.4
Beamwidth, Horizontal, degrees	64	62	58	62	60	59
Beamwidth, Vertical, degrees	10.0	8.9	7.9	8.7	7.5	6.1
Beam Tilt, degrees	0–10	0–10	0–10	0–10	0–10	0–10
USLS (First Lobe), dB	18	18	18	17	17	18
Front-to-Back Ratio at 180°, dB	31	32	30	31	33	34
CPR at Boresight, dB	20	23	20	23	20	13
CPR at Sector, dB	12	15	11	13	10	3
Isolation, Cross Polarization, dB	25	25	25	25	25	25
Isolation, Inter-band, dB	30	30	30	30	30	30
VSWR   Return Loss, dB	1.43   15.0	1.43   15.0	1.43   15.0	1.5   14.0	1.5   14.0	1.5   14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150	-150
Input Power per Port, maximum, watts	300	300	300	250	250	250
Polarization	±45°	±45°	±45°	±45°	±45°	±45°
Impedance	50 ohm	50 ohm	50 ohm	50 ohm	50 ohm	50 ohm

## Electrical Specifications, BASTA\*

Frequency Band, MHz	698–790	790–890	890–960	1710–1920	1920–2170	2300–2690
Gain by all Beam Tilts, average, dBi	15.6	16.3	16.7	16.1	17.3	18.0
Gain by all Beam Tilts Tolerance, dB	±0.5	±0.4	±0.3	±0.7	±0.6	±0.6
Gain by Beam Tilt, average, dBi	0 °   15.7 5 °   15.6 10 °   15.6	0 °   16.2 5 °   16.3 10 °   16.3	0 °   16.7 5 °   16.7 10 °   16.7	0 °   16.1 5 °   16.1 10 °   16.1	0 °   17.5 5 °   17.4 10 °   17.1	0 °   18.1 5 °   17.9 10 °   17.8
Beamwidth, Horizontal Tolerance, degrees	±3.4	±2.3	±2.6	±3.4	±2.5	±4.4
Beamwidth, Vertical Tolerance, degrees	±0.7	±0.5	±0.2	±0.7	±0.7	±0.6

# R2V4PX310R

USLS, beampeak to 20° above beampeak, dB	18	18	18	18	18	18
Front-to-Back Total Power at 180° ± 30°, dB	26	27	25	30	31	32
CPR at Boresight, dB	20	24	20	23	20	13
CPR at Sector, dB	12	15	11	14	10	2

\* CommScope® supports NGMN recommendations on Base Station Antenna Standards (BASTA). To learn more about the benefits of BASTA, [download the whitepaper Time to Raise the Bar on BSAs](#).

## General Specifications

<b>Operating Frequency Band</b>	1710 – 2690 MHz   698 – 960 MHz
<b>Antenna Type</b>	Sector
<b>Band</b>	Multiband
<b>Performance Note</b>	Outdoor usage

## Mechanical Specifications

<b>RF Connector Quantity, total</b>	12
<b>RF Connector Quantity, low band</b>	4
<b>RF Connector Quantity, high band</b>	8
<b>RF Connector Interface</b>	7-16 DIN Female
<b>Grounding Type</b>	RF connector inner conductor and body grounded to reflector and mounting bracket
<b>Radome Material</b>	ASA, UV stabilized
<b>RF Connector Location</b>	Bottom
<b>Wind Loading, frontal</b>	2,008.0 N @ 150 km/h   45.4 lbf @ 150 km/h
<b>Wind Loading, lateral</b>	101.2 lbf @ 150 km/h   450.0 N @ 150 km/h
<b>Wind Speed, maximum</b>	200 km/h   124 mph

## Dimensions

<b>Length</b>	2490.0 mm   98.0 in
<b>Width</b>	641.0 mm   25.2 in
<b>Depth</b>	244.0 mm   9.6 in
<b>Net Weight, without mounting kit</b>	65.0 kg   143.3 lb

## Remote Electrical Tilt (RET) Information

<b>Input Voltage</b>	10–30 Vdc
<b>Internal RET</b>	High band (4)   Low band (2)
<b>Power Consumption, idle state, maximum</b>	2 W
<b>Power Consumption, normal conditions, maximum</b>	13 W
<b>Protocol</b>	3GPP/AISG 2.0 (Single RET)

# R2V4PX310R

---

**RET Interface** 8-pin DIN Female | 8-pin DIN Male  
**RET Interface, quantity** 2 female | 2 male

## Packed Dimensions

**Length** 2693.0 mm | 106.0 in  
**Width** 739.0 mm | 29.1 in  
**Depth** 400.0 mm | 15.7 in  
**Shipping Weight** 95.0 kg | 209.4 lb

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU  
ISO 9001:2015  
China RoHS SJ/T 11364-2014

### Classification

Compliant by Exemption  
Designed, manufactured and/or distributed under this quality management system  
Above Maximum Concentration Value (MCV)




## Included Products

T-029-GL-E — Adjustable Tilt Pipe Mounting Kit for 2.0"-4.5" (60-115mm) OD round members for panel antennas. Includes 2 clamp sets.  
ATCB-B01-C50 — AISG RET Control Cable, 0.5 m

## \* Footnotes

**Performance Note** Severe environmental conditions may degrade optimum performance



Adjustable Tilt Pipe Mounting Kit for 2.0"-4.5" (60-115mm) OD round members for panel antennas. Includes 2 clamp sets.

## General Specifications

<b>Application</b>	Outdoor
<b>Includes</b>	Brackets   Hardware
<b>Package Quantity</b>	1

## Mechanical Specifications

<b>Color</b>	Silver
<b>Material Type</b>	Galvanized steel
<b>Mechanical Tilt</b>	0°-8°

## Dimensions

<b>Antenna-to-Pipe Distance</b>	85.0 mm   3.3 in
<b>Bracket-to-Bracket Distance</b>	1400.0 mm   55.1 in
<b>Compatible Diameter, maximum</b>	115.0 mm   4.5 in
<b>Compatible Diameter, minimum</b>	60.0 mm   2.4 in
<b>Compatible Length, maximum</b>	2850.0 mm   112.2 in
<b>Compatible Length, minimum</b>	1500.0 mm   59.1 in
<b>Net Weight</b>	6.0 kg   13.2 lb

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant by Exemption
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Above Maximum Concentration Value (MCV)
CE	Compliant with the relevant CE product directives



# ATCB-B01-C50

---



## AISG RET Control Cable, 0.5 m

- Feeds data and power to RET system components
- AISG and RoHS compliant

## Electrical Specifications

<b>EU Certification</b>	CB   CE
<b>Protocol</b>	AISG 1.1   AISG 2.0
<b>Voltage, maximum</b>	300 V

## Product Classification

<b>Product Type</b>	AISG standard cable
---------------------	---------------------

## Mechanical Specifications

<b>AISG Connector A</b>	8-pin DIN Female
<b>AISG Connector A Body Style</b>	Straight
<b>AISG Connector A Standard</b>	IEC 60130-9
<b>AISG Connector B</b>	8-pin DIN Male
<b>AISG Connector B Body Style</b>	Straight
<b>AISG Connector B Standard</b>	IEC 60130-9
<b>Data Conductor Type</b>	0.24 mm <sup>2</sup> (24 AWG) twisted pair
<b>Power Conductor Type</b>	0.82 mm <sup>2</sup> (18 AWG) stranded
<b>Total Conductors, quantity</b>	6
<b>Color</b>	Black

## Environmental Specifications

<b>Climatic Sequence Test Method</b>	IEC 60068-2-14
<b>Cold Exposure Test Method</b>	IEC 60068-2-1
<b>Damp Heat Exposure Test Method</b>	IEC 60068-2-30, Test Condition Db
<b>Heat Exposure Test Method</b>	IEC 60068-2-2
<b>Operating Temperature</b>	-40 °C to +70 °C (-40 °F to +158 °F)
<b>Rain Simulation Test Method</b>	IEC 60068-2-18, Test Condition Ra, Method 1
<b>Relative Humidity</b>	Up to 100%
<b>UV Resistance Test Method</b>	IEC 60068-2-5, Test Condition B
<b>Ingress Protection Test Method</b>	IEC 60529:2001, IP67

## Dimensions

<b>Length</b>	0.5 m   1.6 ft
---------------	----------------

# ATCB-B01-C50

---

**Diameter Over Jacket** 8.000 mm | 0.315 in  
**Net Weight** 0.1 kg | 0.3 lb

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU  
ISO 9001:2015  
China RoHS SJ/T 11364-2014  
CE

### Classification

Compliant by Exemption  
Designed, manufactured and/or distributed under this quality management system  
Above Maximum Concentration Value (MCV)  
Compliant with the relevant CE product directives

