

CV65ASX-V1-M



4-port sector antenna, 2x 790–960 and 2x 1710–2690 MHz, 65° HPBW, RET compatible

- Utilizes AccuRET® actuator(s) on the back of the antenna

OBSOLETE

This product was discontinued on: December 31, 2018

Replaced By

RV65A-M	4-port sector antenna, 2x 694–960 and 2x 1695–2690 MHz, 65° HPBW, RET compatible
RV65A-2X2	4-port sector antenna, 2x 694–960 and 2x 1695–2690 MHz, 65° HPBW, RET compatible

Electrical Specifications

Frequency Band, MHz	790–896	870–960	1710–1880	1850–1990	1920–2180	2300–2500	2500–2690
Gain, dBi	13.8	14.0	16.4	17.0	17.4	17.7	17.2
Beamwidth, Horizontal, degrees	62	58	70	67	64	58	59
Beamwidth, Vertical, degrees	16.5	15.6	7.2	6.8	6.3	5.3	5.1
Beam Tilt, degrees	0–15	0–15	2–12	2–12	2–12	2–12	2–12
USLS (First Lobe), dB	13	13	13	14	15	14	13
Front-to-Back Ratio at 180°, dB	25	21	31	26	27	27	27
CPR at Boresight, dB	19	16	21	21	21	18	17
CPR at Sector, dB	8	7	10	9	9	5	4
Isolation, Cross Polarization, dB	25	25	25	25	25	25	25
Isolation, Inter-band, dB	30	30	30	30	30	30	30
VSWR Return Loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150	-150	-150
Input Power per Port, maximum, watts	350	350	350	350	350	300	300
Polarization	±45°	±45°	±45°	±45°	±45°	±45°	±45°
Impedance	50 ohm	50 ohm	50 ohm	50 ohm	50 ohm	50 ohm	50 ohm

Electrical Specifications, BASTA*

Frequency Band, MHz	790–896	870–960	1710–1880	1850–1990	1920–2180	2300–2500	2500–2690
Gain by all Beam Tilts, average, dBi	13.5	13.6	16.2	16.7	17.0	17.3	16.8
Gain by all Beam Tilts Tolerance, dB	±0.4	±0.4	±0.6	±0.4	±0.7	±0.7	±0.7
Gain by Beam Tilt, average, dBi	0° 13.6 8° 13.5 15° 13.3	0° 13.6 8° 13.8 15° 13.4	2° 16.1 7° 16.3 12° 16.1	2° 16.5 7° 16.8 12° 16.6	2° 16.7 7° 17.1 12° 16.9	2° 17.1 7° 17.5 12° 17.0	2° 16.8 7° 17.0 12° 16.3
Beamwidth, Horizontal Tolerance, degrees	±4.3	±3.1	±4.5	±2.4	±5.1	±4.7	±5.9
Beamwidth, Vertical Tolerance, degrees	±1.1	±1.1	±0.5	±0.4	±0.7	±0.3	±0.4
USLS, beampeak to 20° above beampeak, dB	13	13	13	14	15	13	13

CV65ASX-V1-M

Front-to-Back Total Power at 180° ± 30°, dB	20	19	24	24	25	23	20
CPR at Boresight, dB	19	16	22	21	21	19	17
CPR at Sector, dB	8	7	10	9	9	5	4

* CommScope® supports NGMN recommendations on Base Station Antenna Standards (BASTA). To learn more about the benefits of BASTA, [download the whitepaper Time to Raise the Bar on BSAs.](#)

General Specifications

Operating Frequency Band	1710 – 2690 MHz 790 – 960 MHz
Antenna Type	Sector
Band	Multiband
Performance Note	Outdoor usage

Mechanical Specifications

RF Connector Quantity, total	4
RF Connector Quantity, low band	2
RF Connector Quantity, high band	2
RF Connector Interface	7-16 DIN Female
Color	Light gray
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Radiator Material	Brass Low loss circuit board
Radome Material	Fiberglass, UV resistant
Reflector Material	Aluminum
RF Connector Location	Bottom
Wind Loading, maximum	396.0 N @ 150 km/h 89.0 lbf @ 150 km/h
Wind Speed, maximum	241 km/h 150 mph

Dimensions

Length	1413.0 mm 55.6 in
Width	301.0 mm 11.9 in
Depth	180.5 mm 7.1 in
Net Weight, without mounting kit	14.8 kg 32.6 lb

Packed Dimensions

Length	1600.0 mm 63.0 in
Width	429.0 mm 16.9 in
Depth	299.0 mm 11.8 in
Shipping Weight	26.6 kg 58.6 lb

CV65ASX-V1-M

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

Classification

Compliant by Exemption

Designed, manufactured and/or distributed under this quality management system

Above Maximum Concentration Value (MCV)



Included Products

BSAMNT-OFFSET — Forward Offset Pipe Mounting Kit for 4.5 in (114.3 mm) OD round members

* Footnotes

Performance Note

Severe environmental conditions may degrade optimum performance

BSAMNT-OFFSET



Forward Offset Pipe Mounting Kit for 4.5 in (114.3 mm) OD round members

General Specifications

Application	Outdoor
Includes	Brackets Hardware
Package Quantity	1

Mechanical Specifications

Color	Silver
Material Type	Galvanized steel

Dimensions

Compatible Diameter, maximum	115.0 mm 4.5 in
Compatible Diameter, minimum	60.0 mm 2.4 in
Net Weight	3.5 kg 7.7 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Above Maximum Concentration Value (MCV)
CE	Compliant with the relevant CE product directives

