


ATSBT-TOP-FMC3



Top Smart Bias Tee

- Reduces cable and site lease costs by eliminating the need for AISG home run cables
- Weatherproof AISG connectors
- Intuitive schematics simplify and ensure proper installation
- Enhanced lightning protection plus grounding stud for additional surge protection
- Operates at 10-30 Vdc
- AISG 1.1 and 2.0 compliant
- Uses the 4.3-10 connector which is 40 percent smaller than the 7-16 DIN connector

Electrical Specifications

EU Certification	CE
Protocol	AISG 1.1 AISG 2.0
Antenna Interface Signal	dc Blocked RF
BTS Interface Signal	AISG data dc RF
Interface Protocol Signal	Data dc
Voltage Range	10–30 Vdc
VSWR Return Loss	1.17:1 22 dB, typical
Power Consumption, maximum	0.6 W
RF Power, maximum	250 W @ 1850 MHz 500 W @ 850 MHz
Impedance	50 ohm
Insertion Loss, typical	0.1 dB
3rd Order IMD	-158.0 dBc
3rd Order IMD Test Method	Two +43 dBm carriers
Electromagnetic Compatibility (EMC)	CFR 47 Part 15, Subpart B, Class B EN 55022, Class B ICES-003 Issue 4 CAN/CSA-CEI/IEC CISPR 22:02

Product Classification

Product Type	RET bias tee
---------------------	--------------

General Specifications

Smart Bias Tee Type	10–30 V Top
Operating Frequency Band	694 – 2690 MHz

Mechanical Specifications

Antenna Interface	4.3-10 Male
BTS Interface	4.3-10 Female
AISG Input Connector	8-pin DIN Female

ATSBT-TOP-FMC3


Color	Silver
Grounding Lug Thread Size	M8
Material Type	Aluminum
Lightning Surge Capability	5 times @ -3 kA 5 times @ 3 kA
Lightning Surge Capability Test Method	IEC 61000-4-5, Level X
Lightning Surge Capability Waveform	1.2/50 voltage and 8/20 current combination waveform

Environmental Specifications

Ingress Protection Test Method	IEC 60529:2001, IP66
Operating Temperature	-40 °C to +70 °C (-40 °F to +158 °F)

Interface Port Drawing

ATSBT-TOP-FMC3



Dimensions

Width 94.0 mm | 3.7 in

ATSBT-TOP-FMC3

Depth	50.0 mm 2.0 in
Height	143.00 mm 5.63 in
Net Weight	0.7 kg 1.5 lb

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2015
China RoHS SJ/T 11364-2014
CE

Classification

Compliant by Exemption
Designed, manufactured and/or distributed under this quality management system
Above Maximum Concentration Value (MCV)
Compliant with the relevant CE product directives

