



8-port sector antenna, 4x 790–960 and 4x 1695–2690 MHz, 65° HPBW, 4x RET with manual override. Bands cascaded SRET designed for Site-Sharing purpose (two Operators / Primaries operating their assigned RET’s independently)

- The RET interface comprises two pairs of AISG input/output ports, each pair controlling “one side” of the antenna independently: one pair for the left-hand bands 1 and 3 (R1, Y1); one pair for the right-hand bands 2 and 4 (R2, Y2)
- Integrated Internal Remote Electrical Tilt (RET), with independent control of electrical tilt with manual override on all arrays
- All Internal RET actuators on each antenna side are connected in “Cascaded SRET” configuration

This product will be discontinued on: March 27, 2020

Replaced By

RRZZ-65B-R4

8-port sector antenna, 4x 694–960 and 4x 1427–2690 MHz, 65° HPBW, 4x RET

Electrical Specifications

Frequency Band, MHz	790–862	880–960	1695–1880	1850–1990	1920–2180	2300–2500	2500–2690
Gain, dBi	14.9	15.6	16.6	16.8	17.4	18.1	18.2
Beamwidth, Horizontal, degrees	74	63	63	66	68	62	63
Beamwidth, Vertical, degrees	11.3	10.2	7.6	7.0	6.6	5.6	5.2
Beam Tilt, degrees	0–10	0–10	0–10	0–10	0–10	0–10	0–10
USLS (First Lobe), dB	18	18	18	18	18	18	18
Front-to-Back Ratio at 180°, dB	35	35	34	38	40	39	40
Isolation, Cross Polarization, dB	28	28	28	28	28	28	28
Isolation, Inter-band, dB	28	28	28	28	28	28	28
VSWR Return Loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc	-150	-150	-150	-150	-150	-150	-150
Input Power per Port, maximum, watts	300	300	250	250	250	250	250
Polarization	±45°	±45°	±45°	±45°	±45°	±45°	±45°
Impedance	50 ohm	50 ohm	50 ohm	50 ohm	50 ohm	50 ohm	50 ohm


Electrical Specifications, BASTA*

Frequency Band, MHz	790–862	880–960	1695–1880	1850–1990	1920–2180	2300–2500	2500–2690
Gain by all Beam Tilts, average, dBi	14.7	15.4	16.4	16.5	16.9	17.8	17.9
Gain by all Beam Tilts Tolerance, dB	±0.5	±0.3	±0.4	±0.6	±0.7	±0.5	±0.5
Gain by Beam Tilt, average, dBi	0 ° 14.7 5 ° 14.7 10 ° 14.6	0 ° 15.5 5 ° 15.5 10 ° 15.4	0 ° 16.4 5 ° 16.4 10 ° 16.4	0 ° 16.5 5 ° 16.5 10 ° 16.4	0 ° 16.9 5 ° 16.9 10 ° 16.9	0 ° 17.9 5 ° 17.9 10 ° 17.7	0 ° 17.8 5 ° 17.9 10 ° 17.9
Beamwidth, Horizontal Tolerance, degrees	±4.2	±4.7	±3.3	±7.3	±4.4	±3.4	±2.6
Beamwidth, Vertical Tolerance, degrees	±0.5	±0.4	±0.5	±0.3	±0.5	±0.2	±0.2

USLS, beampeak to 20° above beampeak, dB	18	18	18	18	18	17	18
Front-to-Back Total Power at 180° ± 30°, dB	24	25	27	31	30	31	32
CPR at Boresight, dB	20	18	20	20	18	16	18
CPR at Sector, dB	11	9	9	11	12	11	11

* CommScope® supports NGMN recommendations on Base Station Antenna Standards (BASTA). To learn more about the benefits of BASTA, [download the whitepaper Time to Raise the Bar on BSAs.](#)

Array Layout



Array	Freq (MHz)	Conns	RET (SRET)	AISG RET UID
R1	790-960	1-2	1	ARxxxxxxxxxxxxxxxxx1
R2	790-960	3-4	2	ARxxxxxxxxxxxxxxxxx2
Y1	1695-2690	5-6	3	ARxxxxxxxxxxxxxxxxx3
Y2	1695-2690	7-8	4	ARxxxxxxxxxxxxxxxxx4

Left Bottom Right

(Sizes of colored boxes are not true depictions of array sizes)

General Specifications

Operating Frequency Band	1695 – 2690 MHz 790 – 960 MHz
Antenna Type	Sector
Band	Multiband
Performance Note	Outdoor usage

Mechanical Specifications

RF Connector Quantity, total	8
RF Connector Quantity, low band	4
RF Connector Quantity, high band	4
RF Connector Interface	7-16 DIN Female
Color	Gray
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket

Radiator Material	Low loss circuit board
Radome Material	Fiberglass, UV resistant
Reflector Material	Aluminum
RF Connector Location	Bottom
Wind Loading, frontal	803.0 N @ 150 km/h 180.5 lbf @ 150 km/h
Wind Loading, lateral	275.0 N @ 150 km/h 61.8 lbf @ 150 km/h
Wind Loading, maximum	1040.0 N @ 150 km/h 233.8 lbf @ 150 km/h
Wind Speed, maximum	200 km/h 124 mph

Dimensions

Length	2100.0 mm 82.7 in
Width	498.0 mm 19.6 in
Depth	197.0 mm 7.8 in
Net Weight, without mounting kit	39.0 kg 86.0 lb

Remote Electrical Tilt (RET) Information

Input Voltage	10–30 Vdc
Internal RET	High band (2) Low band (2)
Power Consumption, idle state, maximum	2 W
Power Consumption, normal conditions, maximum	13 W
Protocol	3GPP/AISG 2.0 (Single RET)
RET Interface	8-pin DIN Female 8-pin DIN Male
RET Interface, quantity	2 female 2 male

Packed Dimensions

Length	2286.0 mm 90.0 in
Width	565.0 mm 22.2 in
Depth	312.0 mm 12.3 in
Shipping Weight	60.0 kg 132.3 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Above Maximum Concentration Value (MCV)
CE	Compliant with the relevant CE product directives




Included Products

T-029-GL-E — Adjustable Tilt Pipe Mounting Kit for 2.0"-4.5" (60-115mm) OD round members for panel antennas. Includes 2 clamp sets.

* Footnotes

Performance Note Severe environmental conditions may degrade optimum performance



Adjustable Tilt Pipe Mounting Kit for 2.0"-4.5" (60-115mm) OD round members for panel antennas. Includes 2 clamp sets.

General Specifications

Application	Outdoor
Includes	Brackets Hardware
Package Quantity	1

Mechanical Specifications

Color	Silver
Material Type	Galvanized steel
Mechanical Tilt	0°–8°

Dimensions

Antenna-to-Pipe Distance	85.0 mm 3.3 in
Bracket-to-Bracket Distance	1400.0 mm 55.1 in
Compatible Diameter, maximum	115.0 mm 4.5 in
Compatible Diameter, minimum	60.0 mm 2.4 in
Compatible Length, maximum	2850.0 mm 112.2 in
Compatible Length, minimum	1500.0 mm 59.1 in
Net Weight	6.0 kg 13.2 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Above Maximum Concentration Value (MCV)
CE	Compliant with the relevant CE product directives

