



TTRC Copper Closure, unpressurized, gel sealed, 510 mm sheath opening, for up to 300 pair splices

- Watertight, toolless, torchless and re-usable closure for aerial applications
- Seals unpressurised inline splices in new construction and network maintenance applications up to 600 pairs
- Sealing on both the closure body and a multiple of cables is performed by compressing the gel material between two plastic flanges
- Gel compression is activated by a built-in tensing mechanism

## Product Classification

|                              |                    |
|------------------------------|--------------------|
| <b>Product Type</b>          | Gel sealed closure |
| <b>Product Series</b>        | TTRC               |
| <b>Regional Availability</b> | EMEA               |

## General Specifications

|  |                                  |
|--|----------------------------------|
| <b>Application</b>                     | For use with Polyethylene cables |
| <b>Cable Capacity, maximum</b>         | 2                                |
| <b>Color</b>                           | Black                            |
| <b>Package, quantity</b>               | 1                                |
| <b>Packaging Type</b>                  | Bag   Carton                     |
| <b>Single Cable Diameter, maximum</b>  | 21.00 mm   0.83 in               |
| <b>Single Cable Diameter, minimum</b>  | 10.00 mm   0.39 in               |
| <b>Splice Bundle Diameter, maximum</b> | 92.00 mm   3.62 in               |
| <b>Splicing Capacity, maximum</b>      | 300                              |

## Dimensions

|                               |                      |
|-------------------------------|----------------------|
| <b>Sheet Opening, nominal</b> | 510.00 mm   20.08 in |
|-------------------------------|----------------------|

## Mechanical Specifications

|                           |            |
|---------------------------|------------|
| <b>Cable Sealing Type</b> | Gel filled |
| <b>Closure Style</b>      | In-line    |
| <b>Mount Type</b>         | Strand     |

## Environmental Specifications

|                            |        |
|----------------------------|--------|
| <b>Environmental Space</b> | Aerial |
|----------------------------|--------|

## Regulatory Compliance/Certifications

|               |                       |
|---------------|-----------------------|
| <b>Agency</b> | <b>Classification</b> |
|---------------|-----------------------|

RoHS 2011/65/EU

Compliant

