

FF-65B-R1

4-port sector antenna, 4x 617–806 MHz, 65° HPBW, 1x RET, 600MHz-Ready Antenna Technology



- Supports up to 15° of Mechanical Down Tilt

Electrical Specifications

Frequency Band, MHz	617–698	698–806
Gain, dBi	14.1	14.5
Beamwidth, Horizontal, degrees	66	60
Beamwidth, Vertical, degrees	14.8	13.3
Beam Tilt, degrees	2–14	2–14
USLS (First Lobe), dB	19	17
Front-to-Back Ratio at 180°, dB	34	30
Isolation, Cross Polarization, dB	28	28
Isolation, Inter-band, dB	28	28
VSWR Return Loss, dB	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc		-153
Input Power per Port at 50°C, maximum, watts	250	250
Polarization	±45°	±45°
Impedance	50 ohm	50 ohm

Electrical Specifications, BASTA*

Frequency Band, MHz	617–698	698–806
Gain by all Beam Tilts, average, dBi	13.7	14.1
Gain by all Beam Tilts Tolerance, dB	±0.6	±0.6
Gain by Beam Tilt, average, dBi	2 ° 13.5 8 ° 13.7 14 ° 13.6	2 ° 13.9 8 ° 14.2 14 ° 14.1
Beamwidth, Horizontal Tolerance, degrees	±3.4	±4
Beamwidth, Vertical Tolerance, degrees	±1	±1
USLS, beampeak to 20° above beampeak, dB	18	17
Front-to-Back Total Power at 180° ± 30°, dB	23	21
CPR at Boresight, dB	21	26
CPR at Sector, dB	7	9

* CommScope® supports NGMN recommendations on Base Station Antenna Standards (BASTA). To learn more about the benefits of BASTA, [download the whitepaper Time to Raise the Bar on BSAs](#).

General Specifications

Operating Frequency Band 617 – 806 MHz

FF-65B-R1

Antenna Type	Sector
Band	Single band
Performance Note	Outdoor usage
Total Input Power, maximum	900 W @ 50 °C

Mechanical Specifications

RF Connector Quantity, total	4
RF Connector Quantity, low band	4
RF Connector Interface	4.3-10 Female
Color	Light gray
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Radiator Material	Aluminum Low loss circuit board
Radome Material	Fiberglass, UV resistant
RF Connector Location	Bottom
Wind Loading, frontal	172.0 lbf @ 150 km/h 765.0 N @ 150 km/h
Wind Loading, lateral	251.0 N @ 150 km/h 56.4 lbf @ 150 km/h
Wind Loading, maximum	1,041.0 N @ 150 km/h 234.0 lbf @ 150 km/h
Wind Speed, maximum	241 km/h 150 mph

Dimensions

Length	1830.0 mm 72.0 in
Width	640.0 mm 25.2 in
Depth	235.0 mm 9.3 in
Net Weight, without mounting kit	39.5 kg 87.1 lb

Remote Electrical Tilt (RET) Information

Input Voltage	10–30 Vdc
Internal RET	Low band (1)
Power Consumption, idle state, maximum	1 W
Power Consumption, normal conditions, maximum	10 W
Protocol	3GPP/AISG 2.0 (Single RET)
RET Interface	8-pin DIN Female 8-pin DIN Male
RET Interface, quantity	1 female 1 male

Packed Dimensions

Length	1982.0 mm 78.0 in
Width	752.0 mm 29.6 in
Depth	387.0 mm 15.2 in

Shipping Weight

50.5 kg | 111.3 lb

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

ISO 9001:2015

China RoHS SJ/T 11364-2014

Classification

Compliant by Exemption

Designed, manufactured and/or distributed under this quality management system

Above Maximum Concentration Value (MCV)



Included Products


BSAMNT-4 — Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

* Footnotes

Performance Note

Severe environmental conditions may degrade optimum performance

BSAMNT-4



Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

General Specifications

Application	Outdoor
Includes	Brackets Hardware
Package Quantity	1

Mechanical Specifications

Color	Silver
Material Type	Galvanized steel

Dimensions

Compatible Diameter, maximum	115.0 mm 4.5 in
Compatible Diameter, minimum	60.0 mm 2.4 in
Net Weight	6.6 kg 14.6 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant by Exemption
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system
China RoHS SJ/T 11364-2014	Above Maximum Concentration Value (MCV)

