

FFHH-65A-R3

8-port sector antenna, 4x 617-806 and 4x 1695-2360 MHz, 65° HPBW, 3x RET, 600 MHz-Ready Antenna Technology



Electrical Specifications

Frequency Band, MHz	617-698	698-806	1695-1880	1850-1990	1920-2200	2300-2360
Gain, dBi	12.9	13.4	16.6	17.1	17.9	18.4
Beamwidth, Horizontal, degrees	65	61	67	63	60	52
Beamwidth, Vertical, degrees	20.7	19.1	8.0	7.5	7.0	6.2
Beam Tilt, degrees	5-22	5-22	2-12	2-12	2-12	2-12
USLS (First Lobe), dB	15	14	16	17	18	18
Front-to-Back Ratio at 180°, dB	29	30	38	36	37	39
Isolation, Cross Polarization, dB	25	25	25	25	25	25
Isolation, Inter-band, dB	25	25	25	25	25	25
VSWR Return Loss, dB	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0	1.5 14.0
PIM, 3rd Order, 2 x 20 W, dBc		-153	-153	-153	-153	-153
Input Power per Port at 50°C, maximum, watts	250	250	200	200	200	200
Polarization	±45°	±45°	±45°	±45°	±45°	±45°
Impedance	50 ohm	50 ohm	50 ohm	50 ohm	50 ohm	50 ohm

Electrical Specifications, BASTA*

Frequency Band, MHz	617-698	698-806	1695-1880	1850-1990	1920-2200	2300-2360
Gain by all Beam Tilts, average, dBi	12.6	12.8	16.1	16.9	17.3	18.1
Gain by all Beam Tilts Tolerance, dB	±0.6	±0.8	±0.7	±0.4	±0.6	±0.5
Gain by Beam Tilt, average, dBi	5 ° 12.8 14 ° 12.7 22 ° 12.1	5 ° 13.2 14 ° 12.9 22 ° 12.0	2 ° 16.1 7 ° 16.2 12 ° 15.8	2 ° 16.9 7 ° 17.0 12 ° 16.6	2 ° 17.1 7 ° 17.4 12 ° 17.0	2 ° 17.9 7 ° 18.3 12 ° 17.7
Beamwidth, Horizontal Tolerance, degrees	±6.5	±5	±4.2	±4.2	±6.2	±5.8
Beamwidth, Vertical Tolerance, degrees	±1.5	±1.8	±0.5	±0.5	±0.6	±0.3
USLS, beampeak to 20° above beampeak, dB			14	15	15	15
Front-to-Back Total Power at 180° ± 30°, dB	21	20	31	31	31	30
CPR at Boresight, dB	18	18	17	18	18	19
CPR at Sector, dB	7	5	9	7	8	8

* CommScope® supports NGMN recommendations on Base Station Antenna Standards (BASTA). To learn more about the benefits of BASTA, [download the whitepaper Time to Raise the Bar on BSAs](#).

Array Layout



Left Bottom Right

Array	Freq (MHz)	Conns	RET (SRET)	AISG RET UID
R1	617-806	1-2	1	ANxxxxxxxxxxxxxxxxx1
R2	617-806	3-4		
Y1	1695-2360	5-6	2	ANxxxxxxxxxxxxxxxxx2
Y2	1695-2360	7-8	3	ANxxxxxxxxxxxxxxxxx3

(Sizes of colored boxes are not true depictions of array sizes)

Port Configuration



General Specifications

Operating Frequency Band

1695 – 2360 MHz | 617 – 806 MHz

FFHH-65A-R3

Antenna Type	Sector
Band	Multiband
Performance Note	Outdoor usage
Total Input Power, maximum	900 W @ 50 °C

Mechanical Specifications

RF Connector Quantity, total	8
RF Connector Quantity, low band	4
RF Connector Quantity, high band	4
RF Connector Interface	4.3-10 Female
Color	Light gray
Grounding Type	RF connector inner conductor and body grounded to reflector and mounting bracket
Radiator Material	Aluminum Low loss circuit board
Radome Material	Fiberglass, UV resistant
Reflector Material	Aluminum
RF Connector Location	Bottom
Wind Loading, maximum	688.0 N @ 150 km/h 154.7 lbf @ 150 km/h
Wind Speed, maximum	241 km/h 150 mph

Dimensions

Length	1224.0 mm 48.2 in
Width	640.0 mm 25.2 in
Depth	235.0 mm 9.3 in
Net Weight, without mounting kit	33.0 kg 72.8 lb

Remote Electrical Tilt (RET) Information

Input Voltage	10–30 Vdc
Internal RET	High band (2) Low band (1)
Power Consumption, idle state, maximum	1 W
Power Consumption, normal conditions, maximum	10 W
Protocol	3GPP/AISG 2.0 (Single RET)
RET Interface	8-pin DIN Female 8-pin DIN Male
RET Interface, quantity	1 female 1 male

Packed Dimensions

Length	1379.0 mm 54.3 in
Width	752.0 mm 29.6 in
Depth	387.0 cm 152.4 in

FFHH-65A-R3

Shipping Weight

49.5 kg | 109.1 lb

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU
ISO 9001:2015
China RoHS SJ/T 11364-2014

Classification

Compliant by Exemption
Designed, manufactured and/or distributed under this quality management system
Above Maximum Concentration Value (MCV)



Included Products

BSAMNT-4 — Wide Profile Antenna Downtilt Mounting Kit for 2.4 - 4.5 in (60 - 115 mm) OD round members. Kit contains one scissor top bracket set and one bottom bracket set.

* Footnotes

Performance Note

Severe environmental conditions may degrade optimum performance