



TRAC Copper Closure, unpressurized, gel sealed, 22 inch sheath opening, 33 inch long

- Toolless, extendable and re-enterable closure for freebreathing aerial applications
- Consists of three main components: a central body and two end pieces and self support bond system
- Unique convoluted design provides both mechanical and environmental protection
- Recommended for use on polyethylene insulated cable jackets for straight and branch configurations

Product Classification

Product Type	Gel sealed closure
Product Series	TRAC
Regional Availability	Latin America North America

General Specifications

Application	For use with Polyethylene cables
Cable Capacity, maximum	2
Color	Black
Package, quantity	1
Packaging Type	Bag Carton
Single Cable Diameter, maximum	66.04 mm 2.60 in
Splice Bundle Diameter, maximum	177.80 mm 7.00 in
Splicing Capacity, maximum	1200

Dimensions

Length	838.20 mm 33.00 in
Sheet Opening, nominal	558.80 mm 22.00 in

Mechanical Specifications

Cable Sealing Type	Gel filled
Closure Style	In-line
Mount Type	Strand

Environmental Specifications

Environmental Space	Aerial
----------------------------	--------

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant

